

PRODUCT SHEET

Sta-Kon® BAT22-6NV2

Charge ahead — power through every job with the crimp tool that comes with all these extras.



Sta-Kon® BAT22-6NV2

More charge at no extra charge.

Keep on crimping with the Sta-Kon BAT22-6NV2 electromechanical crimping tool. It comes with an extra battery, a charger and a handy carrying case. All so you can carry the day.

01 The STA-KON BAT22-6NV2. Charge ahead.



01

The go-to kit for panel builders, system integrators, electrical contractors, OEMs and MROs, the BAT22-6NV2 delivers outstanding performance in a wide range of industries from data centers to utilities to rail.

It's the complete package:

- Exclusive UL listing*
- Extra battery, charger and carrying case included
- Powerful lithium-ion batteries with charge level indicator
- Single-lever motorized operation for easy manual preclamping, automatic crimping and auto-retract functions
- Extremely light and super fast
- Motor stall protection in case of faulty operation
- LED task illumination

*When used with UL listed die sets.



Cat. no.	Product description
BAT22-6NV2 [†]	Electromechanical crimping tool
RAML1	Battery 10.8 V/1.5 Ah, Li-on (16,2 Wh)
LGML1110	Charger for 10.8 V Li-on batteries, 230 V
Cat. no. — die sets	Product description
DIE2001	Sta-Kon insulated 22–10 AWG terminals
DIE2002	Non-insulated 22–10 AWG terminals
DIE2500	Spec-Kon insulated 22–10 AWG terminals
DIE2007	Insulated 8–6 AWG tubular terminals
DIE1806*	Dragon Tooth® 22F, L, R-6 series
DIE1804*	Dragon Tooth 22L004
DIE1802*	Dragon Tooth 22L002
DIE1801*	Dragon Tooth 22Fm L R-1 Series
DIE2005*	Sta-Kon non-insulated terminals, disconnects and splices 16–6 AWG (8–6 AWG tubular-style terminals only)
DIE2009*	Insulated pressure splicing connectors

[†]Includes 2 batteries, 1 charger and case.

*Not UL or CSA listed.