



EVA-DLO

Self-contained 2 watt, white maintained surface mount led luminaire, including automatic self test, series Evago. Light distribution: long (L), for example hallways, RAL9003

Product Information

Type	EVA-DLO
Catalog number	5520217051
Category_	Escape route lighting
GTIN	08713812763712
GID	7TCA091160R0378
Serie	Evago
Warranty (Year)	5



Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Surface
Material housing	Aluminium / plastic
Colour housing	White
Material	Aluminium / polycarbonate
Colour	White
Length (mm)	150
Width (mm)	150
Height/depth (mm)	35
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Battery	NiMH
Monitoring equipment	Automatic self test
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Light output in emergency operation (lm)	203
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5600
CRI	70
Protection class	II
Degree of protection (IP)	54
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Power consumption maintained mode (W)	3 / 2
Apparent power consumption maintained mode (VA)	3,5 / 2,85
Nominal current (mA)	15
Powerfactor	0,85 / 0,7
Temperature range (°C)	5 ~ +35

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30901
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	0,961
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	225 x 170 x 62