

PRODUCT SPECIFICATION

SR2-DSB-230

Serenga 2 230v AC Spotlite IP42 Recess

Catalogue Number **SR2-DSB-230**GID **7TCA304050R0019**Warranty **4 Year/s Refer to ABB warranty terms & conditions**Power Supply System **Mains / Slave Operation**Mounting Method/Form **Ceiling Recessed**Housing Material **Aluminium/Plastic**Colour **White**Dimensions (LxWxD) **226 x 100 x 38 mm**Temperature Range **0 to 40°C**Weight **0.381 Kg**Nominal Voltage **220-240v AC 50/60Hz**Emergency Duration (Hours) **Mains / Central Battery Hours**Battery **Mains / Central Battery**Monitoring Equipment **None**Lamp **1 x 2W LED**Light output in Emergency Operation **203 Lumens**Average Lifespan light source (hours) **100000 Hours**Light Colour/Temperature/CRI **White / 5600 / 70**Degree of Protection **IP 42 IK tbc**Wiring System **Mains / CBU**Type of Legend **Not Applicable**Exit Sign Viewing/Recognition Distance (m) **Not Applicable**Power Consumption **5.5 VA / 5 Watts**Nominal Current **24 (mA)**Inrush Current **tbc A to 0.1 ms****Accessories****SR2-LENS1** Lens A Escape route 2-4M Ceiling mount**SR2-LENS2** Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M Ceiling mount**SR2-LENS3** Lens C Escape route 8-12M Ceiling mount**SR2-LENS4** Lens D Open Area 2-4M Ceiling mount**SR2-LENS5** Lens E Open Area 4-8M Ceiling mount**SR2-LENS6** Lens E Open Area 8-12M Ceiling mount**SR2-LENS7** Lens G Escape route 2-4M Wall mount