



## SOLO-P/ZT

Self-contained 3 hours 2 watt, maintained surface mount led luminaire, including automatic self test, series Solo. The luminaire is including the pictogram escape route straight forward - right and left (TS 250/51 - /52 and /53).

### Product Information

Type	SOLO-P/ZT
Catalog number	6331031
Category_	Escape route signalisation
GTIN	08713812762340
GID	7TCA091160R0343
Serie	Solo
Warranty (Year)	2



### Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Ceiling;Wall
Mounting form	Surface
Material housing	Plastic
Colour housing	White
Material cover	Plastic, opal
Material	Polycarbonate
Colour	White
Length (mm)	269
Width (mm)	46
Height/depth (mm)	190
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	3
Battery	NiMH
Monitoring equipment	Automatic self test
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Average lifespan light source (hours)	50.000
Colour of light	White
Colour temperature (K)	5000
CRI	80
Protection class	II
Degree of protection (IP)	54
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Sticker
Recognition distance (m)	25
Circuit	Other
Power consumption maintained mode (W)	3,66
Apparent power consumption maintained mode (VA)	4
Nominal current (mA)	17,59
Powerfactor	0,9

Temperature range (°C) 5 ~ +25

**Article Details**

Product class	Emergency luminaire
E-code	EC001957
Discount group	30901
Harmonized code	9405408440
GLN	8713812000008

**Ordering information**

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

**Supply Information**

Weight (kg)	0,827
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	285 x 195 x 50