

PRODUCT SPECIFICATION

# IND1LSLTC

## Indulux 230v AC IP68 EMEX Test Surface

Catalogue Number **IND1LSLTC**  
GID **7TCA091720R0180**  
Warranty **4 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Mains / Slave Operation**  
Mounting Method/Form **Ceiling, Wall Surface**  
Housing Material **316L stainless steel/plastic**  
Colour **Silver/Clear**  
Dimensions (LxWxD) **398 x 100 x 100 mm**  
Temperature Range **-25 to +40°C**  
Weight **1.4 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**  
Battery **Mains / Central Battery**  
Monitoring Equipment **EMEX test**  
Lamp **1 x 5W LED**  
Emergency Light Output (Lumens) **400**  
Average Lifespan light source (Hours) **60000 Hours**  
Light Colour/Temperature/CRI **White / 6000 / 80**  
Degree of Protection **IP68 IK10**

Type of Legend **Single or Double Sided**  
Exit Sign Viewing/Recognition Distance (m) **17**  
Nominal Voltage **220-240v AC 50/60Hz**  
Power Consumption **14 VA / 13 Watts**  
Current **Nominal: 60mA (mA) Inrush: 2A**

### Accessories

**102601K** Cable Entry Cover kit  
**102702K**



Configurable pictograms included



Luminaire

