

PRODUCT SPECIFICATION

# CLQ1LA1

## Camarque 110-230V AC/DC IP20 Surface

Catalogue Number **CLQ1LA1**  
GID **7TCA091130R0542**  
Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Mains / Slave Operation**  
Mounting Method/Form **Ceiling, Wall Surface**  
Housing Material **Plastic**  
Colour **White**  
Dimensions (LxWxD) **348 x 348 x 122 mm**  
Temperature Range **0 to 40°C**  
Weight **1.7 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**  
Battery **Mains / Central Battery**  
Monitoring Equipment **None**  
Lamp **1 x 20W LED**  
Emergency Light Output (Lumens) **1830**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 4000 / 80**  
Degree of Protection **IP20**

Type of Legend **Not Applicable**  
Exit Sign Viewing/Recognition Distance (m) **Not Applicable**  
Nominal Voltage **110-230v AC/DC 0-60Hz**  
Power Consumption **20.8 VA / 19.5 Watts**  
Current **Nominal: 86mA (mA) Inrush: 0.8A**

### Accessories

**CLQ/SR** Semi-recessing kit

**CLQ/GA** Gold Angled Trim

**CLQ/SA** Silver Angled Trim

**CLQ/WA** White Angled Trim

**CLQ/BKA** Black Angled Trim



Luminaire with Silver Angled Trim  
CLQ1LA1 + CLQ/SA



Luminaire  
CLQ1LA1

