

Product Specification

Indulux



Luminaire

IND1LS5DSLTC

Indulux LED D/S 230V LTC

Catalogue Number
Category
GTIN
GID
Warranty (Year)
Other

IND1LS5DSLTC
Combined Escape route or Sign Luminaire
05415022466829
7TCA091720R0177
3
Refer to ABB warranty terms & conditions



Configurable pictograms included

Power Supply System
Mounting Method
Mounting Form
Material Housing
Colour Housing
Material Cover
Material
Colour
Length (mm)
Width (mm)
Height/depth (mm)
Nominal Voltage (V)
Voltage Type
Duration (hours)
Battery
Monitoring Equipment
Lamp Type
Lamp Power
Number of Lamps
Light output in Emergency Operation (lm)
Average Lifespan light source (hours)
Colour of Light
Colour Temperature (K)
CRI
Degree of Protection (IP)
Impact Strength (IK)
Wiring System
Type of Legend

Mains / Slave Operation
Ceiling, Wall
Surface
316L stainless steel/plastic
White/Grey
No cover supplied
316L stainless steel/plastic
Silver/Clear
398
100
100
220-240
AC 50/60Hz
Mains / Central Battery
Mains / Central Battery
EMEX test
LED
10
2
800
60000
White
6000
80
68
10
Mains / CBU
Varies

Legend style	Internal Foil supplied
Recognition distance (m)	17
Power Consumption Maintained mode (W)	6.5
Power Consumption Maintained mode (VA)	7
Nominal current (mA)	30
Inrush Current (A to 0.1ms)	2
Power Factor	0.92
Temperature range (°C)	-25 to +40°C
Weight (Kg)	1.4
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	430 x 130 x 140

Accessories

102601K Cable Entry Cover kit

102702K Battery replacement