



Product type	
Function	Escape route signage and
Product type	Self-contained luminaire
Operating mode	Maintained and non-
Battery type	NiCd

Product information	
Operating time	3 h
Viewing distance	24 m
Functional testing	Naveo®Pro
Max. mounting height	-
Mounting	Wall and ceiling
Mounting type	Surface mounted
Housing colour	White
Housing material	Plastic

Technical data			
Width mm	170	Lamp type	LED
Height mm	195	Input voltage	220-240 V, 50 Hz
Length mm	381	Degree of protection	IP65
Weight g	1660	Isolation class	II
Color temperature K	6500	Impact strength	IK10
Lumen output	96	Ambient temperature	0°C...35°C

Trade mark CE  
 Certification ENEC

We reserve the right to make technical changes to the products and the content of this document at any time without notice. In the case of orders, the agreed qualities are decisive. ABB assumes no responsibility for any errors or omissions in this document. We reserve all rights in this document and the items and illustrations contained therein. Reproduction, disclosure to third parties or use of its content - including parts - is prohibited without the prior written consent of ABB.