



ELDS| MEDIUM VOLTAGE INDOOR APPARATUS

ANSI Medium Voltage Circuit Breakers

Product Family Overview

ANSI MV Circuit Breakers

Product Family



Product name	ADVAC	ADVAC 38	AMVAC	ADVAC G
Voltage	Up to 15 kV	Up to 38 kV	Up to 27kV	Up to 15kV
Continuous Current	Up to 4000 A*	Up to 3000 A*	Up to 4000 A*	Up to 4000A*
Interrupting Current	Up to 63 kA	Up to 40 kA	Up to 50kA	Up to 50kA
Actuation	Spring	Spring	Magnetic	Spring
Racking Mechanism	Manual & Motorized Remote	Manual & Motorized Remote	Manual & Motorized Remote	Manual & Motorized Remote
Execution	Fixed and Draw out	Fixed and Draw out	Fixed and Draw out	Draw out
Footprint	36 in	40 in	36 in	36 in

* With forced air cooling for highest rating only

ABB