

## DIN-modulært

### Jordfeilautomater 2 polt

#### Jordfeilautomater C kar 2 polt

|         |  |
|---------|--|
| 1629833 | JORDFEILAUTOMAT DS202CRM C6A 30mA          |
| 1629808 | JORDFEILAUTOMAT DS202CRM C10A 30mA         |
| 1629801 | JORDFEILAUTOMAT DS202CRM Ck10A 30mA i2=1,4 |
| 1629818 | JORDFEILAUTOMAT DS202CRM C13A 30mA         |
| 1629817 | JORDFEILAUTOMAT DS202CRM Ck13A 30mA i2=1,4 |
| 1629810 | JORDFEILAUTOMAT DS202CRM C16A 30mA         |
| 1629803 | JORDFEILAUTOMAT DS202CRM Ck16A 30mA i2=1,2 |
| 1629812 | JORDFEILAUTOMAT DS202CRM C20A 30mA         |
| 1629805 | JORDFEILAUTOMAT DS202CRM Ck20A 30mA i2=1,3 |
| 1629814 | JORDFEILAUTOMAT DS202CRM C25A 30mA         |
| 1629822 | JORDFEILAUTOMAT DS202CRM C32A 30mA         |
| 1629824 | JORDFEILAUTOMAT DS202CRM C40A 30mA         |

#### Jordfeilautomater 48 pakning

|         |   |
|---------|---|
| 1629858 | JORDFEILAUTOMAT DS202CRM C16A 30mA BULK         |
| 1629857 | JORDFEILAUTOMAT DS202CRM Ck16A 30mA i2=1,2 BULK |

#### AFDD modul for DS202CR

|         |                        |
|---------|------------------------|
| 1629896 | AFDD modul for DS202CR |
|---------|------------------------|

### 3 polt jordfeilautomat

#### 3 polt Jordfeilautomat for IT nett (4moduler) Standard type

|         |                                       |
|---------|---------------------------------------|
| 1623957 | JORDFEILAUTOMAT DS203NC C10/30mA 230V |
| 1623959 | JORDFEILAUTOMAT DS203NC C16/30mA 230V |
| 1623960 | JORDFEILAUTOMAT DS203NC C20/30mA 230V |
| 1623961 | JORDFEILAUTOMAT DS203NC C25/30mA 230V |
| 1623962 | JORDFEILAUTOMAT DS203NC C32/30mA 230V |

#### Jordfeilbryter type B for Elbil ( Høye startstrømmer, støy immun)

|         |                                       |
|---------|---------------------------------------|
| 1672356 | JORDFEILBRYTER F202 B 25A/30mA 2 polt |
| 1672357 | JORDFEILBRYTER F202 B 40A/30mA 2 polt |
| 1672371 | JORDFEILBRYTER F204 B 40A/30mA 4 polt |

#### Jordfeilbrytere

|         |  |
|---------|--|
| 1662901 | JORDFEILBRYTER F202 A 25A/30mA 2 polt  |
| 1662907 | JORDFEILBRYTER F204 A 25A/30mA 4 polt  |
| 1662911 | JORDFEILBRYTER F204 A 63A/30mA 4 polt  |
| 1662969 | JORDFEILBRYTER F204 A 63A/100mA 4 polt |

### Overspenningsvern

#### Overspenningvern for IT nett og luftstrekk

|         |                                       |
|---------|---------------------------------------|
| 1672318 | OVR T2 3L 40-440 P TS QS m/Signalkont |
| 1672317 | OVR T2 3L 40-440 P QS                 |
| 1672314 | OVR T2 2L 40-440 P TS QS m/Signalkont |
| 1672313 | OVR T2 2L 40-440 P QS                 |

#### Overspenningvern for TN/TT nett 3 polt

|         |                                       |
|---------|---------------------------------------|
| 1672316 | OVR T2 3L 40-275 P TS QS m/Signalkont |
| 1672315 | OVR T2 3L 40-275 P QS                 |

### Lastbrytere

|         |                              |
|---------|------------------------------|
| 1429486 | MODULÆR LASTBRYTER SD202/63  |
| 1429490 | MODULÆR LASTBRYTER SD203/40  |
| 1429492 | MODULÆR LASTBRYTER SD203/63  |
| 1424329 | MODULÆR LASTBRYTER E203/80r  |
| 1424330 | MODULÆR LASTBRYTER E203/100r |
| 1429496 | MODULÆR LASTBRYTER SD204/40  |
| 1429498 | MODULÆR LASTBRYTER SD204/63  |

### Tilbehør din modulære produkter

#### Tilbehør

|         |                           |
|---------|---------------------------|
| 1633794 | ADAPTER FOR PADLOCK, SA 1 |
| 1629897 | Lås for DS202CR           |
| 1633770 | JORDINGSLIST KLB 16       |
| 1633771 | JORDINGSLIST KLB 24       |
| 2437819 | KABELKLEMMER OZXT1        |

#### Ringetrafo

|         |                     |
|---------|---------------------|
| 5469052 | RINGETRAFO TM 15/12 |
|---------|---------------------|

### Jordfeilautomater B kar 2 polt

|         |  |
|---------|--|
| 1629834 | JORDFEILAUTOMAT DS202CRM B6A 30mA          |
| 1629809 | JORDFEILAUTOMAT DS202CRM B10A 30mA         |
| 1629800 | JORDFEILAUTOMAT DS202CRM Bk10A 30mA i2=1,4 |
| 1629819 | JORDFEILAUTOMAT DS202CRM B13A 30mA         |
| 1629816 | JORDFEILAUTOMAT DS202CRM Bk13A 30mA i2=1,4 |
| 1629811 | JORDFEILAUTOMAT DS202CRM B16A 30mA         |
| 1629802 | JORDFEILAUTOMAT DS202CRM Bk16A 30mA i2=1,2 |
| 1629813 | JORDFEILAUTOMAT DS202CRM B20A 30mA         |
| 1629804 | JORDFEILAUTOMAT DS202CRM Bk20A 30mA i2=1,3 |
| 1629815 | JORDFEILAUTOMAT DS202CRM B25A 30mA         |
| 1629823 | JORDFEILAUTOMAT DS202CRM B32A 30mA         |
| 1629825 | JORDFEILAUTOMAT DS202CRM B40A 30mA         |

#### Jordfeilautomater APR kortforsink/støymimmun.

|         |  |
|---------|--|
| 1629867 | JORDFEILAUTOMAT DS202CRM B16A 30mA APR |
| 1629862 | JORDFEILAUTOMAT DS202CRM C10A 30mA APR |
| 1629866 | JORDFEILAUTOMAT DS202CRM C16A 30mA APR |
| 1629872 | JORDFEILAUTOMAT DS202CRM C32A 30mA APR |
| 1629875 | JORDFEILAUTOMAT DS202CRM B40A 30mA APR |
| 1629874 | JORDFEILAUTOMAT DS202CRM C40A 30mA APR |

### 4 polt jordfeilautomat 3+N

#### Jordfeilautomater 3+N for TN (4moduler)

|         |                                       |
|---------|---------------------------------------|
| 1683600 | JORDFEILAUTOMAT DS203NC C10/30mA      |
| 1683602 | JORDFEILAUTOMAT DS203NC C16/30mA      |
| 1683603 | JORDFEILAUTOMAT DS203NC C20/30mA      |
| 1683604 | JORDFEILAUTOMAT DS203NC C25/30mA      |
| 1683605 | JORDFEILAUTOMAT DS203NC C32/30mA      |
| 1683642 | JORDFEILAUTOMAT DS203NC C16/30mA AP-R |
| 1683610 | JORDFEILAUTOMAT DS203NC C16/100mA     |
| 1683611 | JORDFEILAUTOMAT DS203NC C20/100mA     |
| 1683612 | JORDFEILAUTOMAT DS203NC C25/100mA     |
| 1683613 | JORDFEILAUTOMAT DS203NC C32/100mA     |

#### Signal/Hjelpe kontakt

|         |  |
|---------|--|
| 1665770 | SIGNAL/HJELPEKONTAKT S2C-SH6R          |
| 1665769 | HJELPEKONTAKT S2C-H6R                  |
| 1683145 | Hjelpekontakt(H) for DS202CR           |
| 1683146 | Hjelpe-/signalkontakt(S/H) for DS202CR |

#### Overspenningvern for TN/TT nett 2 polt L+N

|         |                                       |
|---------|---------------------------------------|
| 1672312 | OVR T2 1N 40-275 P TS QS m/Signalkont |
| 1672311 | OVR T2 1N 40-275 P QS                 |

#### Overspenningvern for TN/TT nett 4 polt

|         |                                       |
|---------|---------------------------------------|
| 1672321 | OVR T2 3N 40-275 P TS QS m/Signalkont |
| 1672320 | OVR T2 3N 40-275 P QS                 |

### Modulære kontaktorer

#### Modulære kontaktorer 2 polt, 1 modul

|         |                        |
|---------|------------------------|
| 4190228 | KONTAKTOR ESB20-20N-01 |
| 4190231 | KONTAKTOR ESB20-20N-06 |

#### Modulære kontaktorer 4 polt, 2 modul

|         |                        |
|---------|------------------------|
| 4190246 | KONTAKTOR ESB25-40N-01 |
| 4190249 | KONTAKTOR ESB25-40N-06 |

#### Modulær bryter

|         |                                  |
|---------|----------------------------------|
| 1429731 | BRYTER FOR DIN-SKINNE E211-16-20 |
| 1429735 | BRYTER FOR DIN-SKINNE E211-25-20 |

#### Astrour, med Bluetooth programmering

|         |                     |
|---------|---------------------|
| 1478096 | DWA1 ASTROUR 1KANAL |
| 1478097 | DWA2 ASTROUR 2KANAL |

#### Modulær Stikkontakt

|         |                            |
|---------|----------------------------|
| 1547623 | STIKK FOR DIN-SKINNE M1175 |
|---------|----------------------------|



### OV automat 2 polt

|         |                        |            |
|---------|------------------------|------------|
| 1623971 | OVERLASTVERN S202-OV25 | 2-pol 25A  |
| 1623972 | OVERLASTVERN S202-OV32 | 2-pol 35A  |
| 1623973 | OVERLASTVERN S202-OV40 | 2-pol 40A  |
| 1623974 | OVERLASTVERN S202-OV50 | 2-pol 50A  |
| 1623975 | OVERLASTVERN S202-OV63 | 2-pol 63 A |

### OV automat 4 polt 3+N

|         |                           |               |
|---------|---------------------------|---------------|
| 1623981 | OVERLASTVERN S203-OV25 NA | 3+N 4 pol 25A |
| 1623982 | OVERLASTVERN S203-OV32 NA | 3+N 4 pol 32A |
| 1623983 | OVERLASTVERN S203-OV40 NA | 3+N 4 pol 40A |
| 1623984 | OVERLASTVERN S203-OV50 NA | 3+N 4 pol 50A |
| 1623985 | OVERLASTVERN S203-OV63 NA | 3+N 4 pol 63A |

### Automater

#### C Automat 2 polt

|         |                          |
|---------|--------------------------|
| 1665244 | AUTOMATSIKRING S202M-C6  |
| 1665233 | AUTOMATSIKRING S202M-C10 |
| 1665234 | AUTOMATSIKRING S202M-C13 |
| 1665235 | AUTOMATSIKRING S202M-C16 |
| 1665237 | AUTOMATSIKRING S202M-C20 |
| 1665238 | AUTOMATSIKRING S202M-C25 |
| 1665240 | AUTOMATSIKRING S202M-C32 |
| 1665242 | AUTOMATSIKRING S202M-C40 |

#### C Automat 4 polt

|         |                          |
|---------|--------------------------|
| 1665731 | AUTOMATSIKRING S204M-C10 |
| 1665733 | AUTOMATSIKRING S204M-C16 |
| 1665735 | AUTOMATSIKRING S204M-C20 |
| 1665736 | AUTOMATSIKRING S204M-C25 |
| 1665738 | AUTOMATSIKRING S204M-C32 |
| 1665740 | AUTOMATSIKRING S204M-C40 |
| 1665741 | AUTOMATSIKRING S204M-C50 |
| 1665743 | AUTOMATSIKRING S204M-C63 |



### OV automat 3 polt

|         |                        |           |
|---------|------------------------|-----------|
| 1623976 | OVERLASTVERN S203-OV25 | 3-pol 25A |
| 1623977 | OVERLASTVERN S203-OV32 | 3-pol 32A |
| 1623978 | OVERLASTVERN S203-OV40 | 3-pol 40A |
| 1623979 | OVERLASTVERN S203-OV50 | 3-pol 50A |
| 1623980 | OVERLASTVERN S203-OV63 | 3-pol 63A |

### S800P-OV 80A-125A Icn=25 kA Icu=50 kA

|         |                    |            |
|---------|--------------------|------------|
| 1629248 | AUTOMAT S803P-D80  | 3-pol 80A  |
| 1629249 | AUTOMAT S803P-D100 | 3-pol 100A |
| 1629266 | AUTOMAT S803P-D125 | 3-pol 125A |
| 1629272 | AUTOMAT S804P-D80  | 4-pol 80A  |

### C Automat 3 polt

|         |                          |
|---------|--------------------------|
| 1665541 | AUTOMATSIKRING S203M-C10 |
| 1665545 | AUTOMATSIKRING S203M-C16 |
| 1665549 | AUTOMATSIKRING S203M-C20 |
| 1665551 | AUTOMATSIKRING S203M-C25 |
| 1665555 | AUTOMATSIKRING S203M-C32 |
| 1665559 | AUTOMATSIKRING S203M-C40 |
| 1665561 | AUTOMATSIKRING S203M-C50 |
| 1665565 | AUTOMATSIKRING S203M-C63 |

### Kwh-målere

#### Direktekoblet 3 fas/3+N

|         |                      |                   |
|---------|----------------------|-------------------|
| 8204093 | MÅLER 3F C13 110-300 | 3 FAS (3+N)       |
| 8204067 | MÅLER 3F B23 111-100 |                   |
| 8204068 | MÅLER 3F B23 112-100 | + MODBUS & EQ BUS |
| 8204069 | MÅLER 3F B23 113-100 | + M-BUS           |

#### B-serie trafokoblet 3 fas/3+N (Bygg)

|         |                      |                   |
|---------|----------------------|-------------------|
| 8204074 | MÅLER 3F B24 111-100 |                   |
| 8204075 | MÅLER 3F B24 112-100 | + MODBUS & EQ BUS |
| 8204076 | MÅLER 3F B24 113-100 | + M-BUS           |

#### Direktekoblet 1 fas

|         |                      |                   |
|---------|----------------------|-------------------|
| 8200082 | MÅLER C11 110-301    | IEC 1 FAS 1POL    |
| 8204060 | MÅLER 1F B21 111-100 |                   |
| 8204061 | MÅLER 1F B21 112-100 | + MODBUS & EQ BUS |
| 8204062 | MÅLER 1F B21 113-100 | + M-BUS           |

### Samleskinner

#### Samleskinne 3-FAS

|         |                       |              |
|---------|-----------------------|--------------|
| 1667495 | SKINNE PS3 (L1,L2,L3) | 6mod. 10mm2  |
| 1667496 | SKINNE PS3 (L1,L2,L3) | 9mod. 10mm2  |
| 1665930 | SKINNE PS3 (L1,L2,L3) | 12mod. 10mm2 |
| 1665927 | SKINNE PS3 (L1,L2,L3) | 18mod. 10mm2 |
| 1665931 | SKINNE PS3 (L1,L2,L3) | 60mod. 16mm2 |

#### Samleskinne 3-FAS+N FOR 1+N (jordfeil)Automat 2 polt TN

|         |                             |              |
|---------|-----------------------------|--------------|
| 1665945 | SKINNE PS4 (L1,N,L2,N,L3,N) | 12mod, 10mm2 |
| 1665944 | SKINNE PS4 (L1,N,L2,N,L3,N) | 18mod, 10mm2 |
| 1665946 | SKINNE PS4 (L1,N,L2,N,L3,N) | 58mod, 16mm2 |

#### Samleskinne 2 fas IT, TT

|         |                    |                          |
|---------|--------------------|--------------------------|
| 1643288 | SKINNE PS2 (L1,L2) | 4mod. Overgang OVR 10mm2 |
| 1665920 | SKINNE PS2 (L1,L2) | 12mod, 10mm2             |
| 1665925 | SKINNE PS2 (L1,L2) | 18mod, 10mm2             |
| 1665921 | SKINNE PS2 (L1,L2) | 58mod, 16mm2             |

#### Samleskinne 3-FAS+N FOR 4-moduls (jordfeil) automater

|         |                            |                          |
|---------|----------------------------|--------------------------|
| 1665941 | SKINNE PS4 (L1,L2,L3,N)    | 60mod, 16mm2             |
| 1665940 | SKINNE PS4/12 (L1,L2,L3,N) | 12mod                    |
| 1643290 | SKINNE PS4 (L1,L2,L3,N)    | 8mod. Overgang OVR 10mm2 |

#### Tilbehør samleskinner

|         |                               |
|---------|-------------------------------|
| 1665951 | ENDEKAPPE for 2&3 fas, PS-END |
| 1665952 | ENDEKAPPE for 3+N, PS-END1    |
| 1655776 | AVDEKNING FOR 5 LEDIGE PINNER |

### Samleskinner for ny jordfeilautomat 2 polt

#### Samleskinne 2 fas IT, TT for DS202CR. L1-L2...

|         |                          |               |
|---------|--------------------------|---------------|
| 1629884 | SKINNE 2FAS (L1-L2..)    | 10mm2 12-PINS |
| 1629885 | SKINNE 2FAS (L1-L2..)    | 16mm2 56-PINS |
| 1629886 | SKINNE 2FAS+HJ (L1-L2..) | 10mm2 10-PINS |
| 1629887 | SKINNE 2FAS+HJ (L1-L2..) | 16mm2 46-PINS |
| 1629960 | GAFFELSKINNE L1-L2.      | 18pol, 10mm2  |
| 1629958 | GAFFELSKINNE L1-L2.      | 56pol, 16mm2  |
| 1629952 | GAFFELSKINNE L1-L2-H.    | 10pol, 10mm2  |
| 1629953 | GAFFELSKINNE L1-L2-H.    | 44pol, 10mm2  |

#### Samleskinne 3-FAS for DS202CR. L1-L2-L3...

|         |                          |               |
|---------|--------------------------|---------------|
| 1629893 | SKINNE 3FAS (L1-L2-L3..) | 10mm2 18-PINS |
| 1629894 | SKINNE 3FAS (L1-L2-L3..) | 10mm2 57-PINS |
| 1629895 | SKINNE 3FAS (L1-L2-L3..) | 16mm2 57-PINS |
| 1629959 | GAFFELSKINNE L1-L2-L3.   | 18pol, 10mm2  |
| 1629956 | GAFFELSKINNE L1-L2-L3.   | 57pol, 10mm2  |
| 1629957 | GAFFELSKINNE L1-L2-L3.   | 57pol, 16mm2  |

#### Samleskinne 3+N for DS202CR. L1-N-L2-N-L3-N...

|         |                              |               |
|---------|------------------------------|---------------|
| 1629888 | SKINNE 3+N (L1-N-L2-N-L3-N)  | 10mm2 12-PINS |
| 1629889 | SKINNE 3+N (L1-N-L2-N-L3-N)  | 10mm2 54-PINS |
| 1629890 | SKINNE 3+N (L1-N-L2-N-L3-N)  | 16mm2 54-PINS |
| 1629961 | GAFFELSKINNE L1-N-L2-N-L3-N  | 18pol, 10mm2  |
| 1629954 | GAFFELSKINNE L1-N-L2-N-L3-N. | 54pol 10mm2   |
| 1629955 | GAFFELSKINNE L1-N-L2-N-L3-N. | 54pol 16mm2   |

#### Endekapper/tilkoblingsklemme DS202CR

|         |                                     |
|---------|-------------------------------------|
| 1683150 | ENDEKAPPE 2FAS                      |
| 1683167 | ENDEKAPPE 2/3FAS                    |
| 1683168 | ENDEKAPPE 3+N                       |
| 1629892 | AVDEKNING BR-BS                     |
| 1629891 | TILKOBLINGSKLEMME BR-FS for DS202CR |

For et komplett Sortiment besøk vår søkemotor på nett : [www.abbprodukter.no](http://www.abbprodukter.no)