

Cable accessories and connectors

Cold shrink earthing kit CSE 12-42 kV

For fast and easy installation process

For CSE-A, CSE-B, CSS-B and TP-A, an earthing kit must be used which shall be ordered separately. In 3-core cable earthing kit, cold shrink crutch seal, protective hoses, constant force springs and Cu-braids are included. In 1-core cable earthing kit, cold shrink protective hoses, constant force springs and Cu-braids are included.



Type	Product type	Conductor cross section (mm ²)			
		8.7/15 (17.5) kV	12/20 (24) kV	18/30 (36) kV	26/35 (40.5) kV
3-core with armoring earthing kit	3151-3871CNTHB	25 - 50	25 - 35	-	-
	3151-3872CNTHB	70 - 120	50 - 95	35	-
	3151-3873CNTHB	150 - 240	120 - 185	50 - 95	-
	3151-3874CNTHB	300 - 400	240 - 300	120 - 185	50 - 95
	3151-3875CNTHB	500 - 630	400 - 500	240 - 400	120 - 185
	3151-3876CNTHB	-	630	500 - 630	240 - 400
	3151-3877CNTHB	-	-	-	500 - 630
1-core without armoring earthing kit	3151-3871CNTHB1	25 - 50	25 - 35	-	-
	3151-3872CNTHB1	70 - 120	50 - 95	35	-
	3151-3873CNTHB1	150 - 240	120 - 185	50 - 95	-
	3151-3874CNTHB1	300 - 400	240 - 300	120 - 185	-
	3151-3875CNTHB1	500 - 630	400 - 500	240 - 400	50 - 185
	3151-3876CNTHB1	-	630	500 - 630	240 - 400
	3151-3877CNTHB1	-	-	-	500 - 630

Type	Product type	Conductor cross section (mm ²)			
		8.7/15 (17.5) kV	12/20 (24) kV	18/30 (36) kV	26/35 (40.5) kV
1-core with armoring earthing kit	3151-3871CNTHB2	25 - 50	25 - 35	-	-
	3151-3872CNTHB2	70 - 120	50 - 95	35 - 50	-
	3151-3873CNTHB2	150 - 240	120 - 185	70 - 150	-
	3151-3874CNTHB2	300 - 400	240 - 300	185 - 240	50 - 150
	3151-3875CNTHB2	500 - 630	400 - 630	300 - 400	185 - 300
	3151-3876CNTHB2	-	-	500 - 630	400 - 630
1-core upper wire screen unarmored earthing kit	3151-3871CNTHB-CW	25 - 50	25 - 35	-	-
	3151-3872CNTHB-CW	70 - 120	50 - 95	25	-
	3151-3873CNTHB-CW	150 - 240	120 - 185	35 - 95	25
	3151-3874CNTHB-CW	300 - 400	240 - 300	120 - 240	35 - 95
	3151-3875CNTHB-CW	500 - 630	400 - 630	300 - 400	120 - 240
	3151-3876CNTHB-CW	-	-	500 - 630	300 - 630
Lead sheath submarine cable earthing kit	3151-3875CNTHB-WP	-	-	-	59 - 95
	3151-3876CNTHB-WP	-	-	-	120 - 185
	3151-3877CNTHB-WP	-	-	-	240 - 630

Hitachi Energy High Voltage Switchgear Co., Ltd Beijing
12 Jingyuan Street Beijing Economic Development Area
100176 Beijing
Tel. +86 10 6781 8000

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. Hitachi Energy Ltd. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of Hitachi Energy Ltd.