

PRODUCT SPECIFICATION

STVVE3LS1X

Navigator Compact Self-Contained 32M IP20 Self-Test Wall Surface

Catalogue Number **STVVE3LS1X**
GID **7TCA091160R0570**

Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Wall Surface**
Housing Material **Metal**
Colour **White**
Dimensions (LxWxD) **358 x 185 x 71 mm**
Temperature Range **0 to 30°C**
Weight **1.86 Kg**

Emergency Duration (Hours) **3**
Battery **NiCd**
Monitoring Equipment **Automatic self test**
Lamp **1 x 2W LED**
Emergency Light Output (Lumens) **Not Applicable**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 4000 / 80**
Degree of Protection **IP20**

Type of Legend **Single Sided**
Exit Sign Viewing/Recognition Distance (m) **32**
Nominal Voltage **220-240v AC 50/60Hz**
Power Consumption **6.1 VA / 3.9 Watts**
Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

Accessories

XEN2V31 Down ISO7010 Legend
XEN3V31 Left ISO7010 Legend
XEN6V31 Right ISO7010 Legend
XEN5V31 Up ISO7010 Legend
XB01V31 Arabic English Legend

VEBACK Rear Trim Plate for Ceiling Mount



Exit Sign
STVVE3LS1X + XEN2V31

