




REMOVABLE GLAND PLATE
TYP. TOP & BOTTOM




REAR VIEW



PAD LOCK BRACKET

SOLENOID KEY RELEASE
PANEL

FRONT VIEW
(DOOR REMOVED)



RIGHT SIDE VIEW

NOTES:

1. APPROXIMATE WEIGHT: 400 LBS.
2. ASSEMBLY IS UL/CUL LISTED TO UL 891 AND C22.2 NO. 244.
3. NEMA 1 WALL MOUNT ENCLOSURE.
4. THE BOX AND TRIM ARE CONSTRUCTED OF GALVANIZED STEEL.
5. THE TRIM FINISH IS POWDER COATED ON ALL EXTERNAL AND VISIBLE SURFACES, BOX AND ALL INTERNAL MOUNT BRACKETS ARE GALVANIZED FINISH.
6. THE CABINET IS TO BE MOUNTED THROUGH Ø0.531" HOLES IN THE BACK OF THE ENCLOSURE.



Part#: 79-3000-0000039
 Description: 3B MBP W/ SKRU FOR AVC40- 225KVA, 208VAC
 Voltage: 208/12VAC, 3Ph/4W/G
 Breaker Quantity: (3)
 Breaker Size: 800AT (Setting)/800AF, 100%, 310+ LSI Eaton Series C M-Frame (UIB, MBB, MIB)
 AIC Rating: 65k / Breaker Accessories: Dual Auxiliary Contacts (UIB, MBB, MIB)
 Interlock: 120VAC SKRU with Kirk-Key Locks standard
 Dimensions: 36.0"W x 13.5"D x 48"H / Weight: 165 Lbs / Color: Black (BT)