

PRODUCT SPECIFICATION

IR2OZ3L261

Horizon Self-Contained 25M IP20 IR2 Wall Rec

Catalogue Number **IR2OZ3L261**
GID **7TCA091170R0009**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **Aluminium/Plastic**
Colour **White/Silver**
Dimensions (LxWxD) **364 x 167 x 82 mm**
Temperature Range **0 to 25°C**
Weight **1.3 Kg**

Emergency Duration (Hours) **3 Hours**
Battery **NiCd**
Monitoring Equipment **IR2 test**
Lamp **2 x 2W LED**
Emergency Light Output (Lumens) **Not Applicable**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 6350 / 73**
Degree of Protection **IP40**

Type of Legend **Single Sided (Order separate)**
Exit Sign Viewing/Recognition Distance (m) **25**
Nominal Voltage **220-240v AC 50Hz**
Power Consumption **9.9 VA / 5.1 Watts**
Current **Nominal: 42.5mA (mA) Inrush: 18A**

Accessories

XEN2H Single Sided Down ISO7010 Legend
XEN3H Single Sided Left ISO7010 Legend
XEN6H Single Sided Right ISO7010 Legend
XEN5H Single Sided Up ISO7010 Legend
XB01H Single Sided Arabic English Legend
XLF-SN802 Fire Extinguisher Legend
XLF-SN803 Hose Reel Legend

OH/BCM Ceiling Bracket for Vertical Mount
OH/WG Protective Wire Guard



Exit Sign
IR2OZ3L261 + XEN2H

