



REVISIONS

REV	DESCRIPTION	DATE	APPROVED
1	9800240C	6-22-98	
2	9800240I	7-29-98	
3	R0814582 MSM	03-31-08	



GE PowerMark Gold™ Auxillary Gutter



LISTED CONTROL NO. 48PA AUXILLARY GUTTER

Type 1 Indoor Enclosure
 Cat. No.: **TMAGB43D**

Use only GE type Tap Kits: **TMGT250 or TMGT500 or TMGT750**

1 PHASE OR 3 PHASE 240 VOLT MAXIMUM

SUITABLE FOR USE ON A CIRCUIT CAPABLE OF DELIVERING NOT MORE THAN 65,000 RMS SYMMETRICAL AMPERES AT 240 V.A.C. MAXIMUM.

ONLY FEED-THRU AND PARALLEL TAP CONNECTORS LISTED BELOW ARE TO BE ACCOMODATED IN THIS ENCLOSURE. SUITABLE FOR USE IN ALL GE LOAD CENTERS. TAP KIT ASSEMBLIES ARE ORDERED SEPARATELY.

ACCEPTABLE GUTTER TAP KITS:	MAIN	TAP
TMGT250	250-1/0	250-6
TMGT500	500-350	500-02
TMGT750	750-500	500-02



TAP KIT INSTRUCTIONS:
 TAP LUGS TERMINATIONS REQUIRED WITHIN 18 INCHES OF THE FEED-IN SIDE OF THE AUXILIARY GUTTER.

1. STRIP WIRE PER GAUGE ON PROTECTIVE COVER, SPACING CUTS A MINIMUM OF 2 1/2 INCHES APART. MAKE MAIN AND TAP CONNECTIONS.
2. TORQUE REQUIREMENTS:
 TMGT250 - 325 IN.LBS.; TMGT500 & TMGT750 - 375 IN.LBS.
3. PLACE CONNECTOR WITH WIRES INTO THE PROTECTIVE COVER.
4. SNAP PROTECTIVE COVER CLOSED.

NOTE: BUSHING COUPLER AND MOUNTING BOLTS MUST BE INSTALLED PER INSTRUCTION SHEET PRIOR TO WIRE INSTALLATION.

10080802P6 Plainville, CT 06062 ASSEMBLED IN MEXICO

P6 MAT'L: C50HD15A
 SIZE: 5.00 X 5.00

GE (USA) CONFIDENTIAL AND PROPRIETARY THIS GE DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF GE ELECTRICAL DISTRIBUTION & CONTROL (ED&C). IT IS LOANED ON CONDITION THAT IT AND THE INFORMATION THEREIN SHALL NOT BE USED BY RECIPIENT NOR DISCLOSED TO OTHERS EXCEPT AS EXPRESSLY APPROVED BY ED&C. ANY DOCUMENT CONTAINING SUCH INFORMATION SHALL BE RETURNED ON REQUEST.	FOR ADDITIONAL INFO REFER TO APPLIED PRACTICES	SIGNATURES DRAWN JFN	DATE 6-22-98	 GE Consumer & Industrial
	UNLESS OTHERWISE SPECIFIED	CHECKED		
	DIMENSIONS ARE IN INCHES TOLERANCES ON: PL DECIMALS ± PL DECIMALS ± ANGLES ± FRACTIONS ±	ENGRG MFG QUALITY ISSUED		
	THIRD ANGLE PROJECTION 	DRAWING FILE REFERENCE 10080802P6.tif	SIZE A	
FIRST MADE FOR			SCALE NTS	SHEET 1 OF 1

⊕ CRITICAL TO QUALITY CHARACTERISTIC