



<p>Number of Poles 1, 2, & 3</p> <p>Voltage Rating 240Vac</p> <p>Current Rating 15A to 100A</p> <p>Protection Thermal Magnetic High Magnetic High Intensity Discharge Shunt Trip Accessorized Switching Neutral</p>	<p>Molded Case Circuit Breakers Q-Line: 240V</p>	
<p>*THQL High Magnetic is rated at 120/240Vac</p>	<p>Type Thermal Magnetic: THQL, THHQL, THQB, THHQB, THQC, THHQC High Magnetic: THQL*</p> <p>Operating Conditions: Curve represents cold trip with no prior load. Curves apply at 60 Hertz with reference ambient temperature of 40°C wired with conductors of corresponding rating. Refer to technical guide from the UL catalog for more information regarding thermal application.</p>	<p>Adjustments Long-time delay thermal trip: not adjustable. Instantaneous magnetic trip: not adjustable.</p>