



## AQL 02/24/FR/LED

Slave 1 watt, 24 Volt surface mount led luminaire including heating element, series Aqualux

### Product Information

Type	AQL 02/24/FR/LED
Catalog number	6010953
Category_	Escape route signalisation
GTIN	08713812772332
GID	7TCA304010R0000
Serie	Aqualux
Warranty (Year)	5
Other	The luminaire is equipped with a light dimming circuit, the minimum output is in accordance with the standard



### Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling;Wall
Mounting form	Surface
Material housing	Aluminium / plastic
Colour housing	White / aluminium
Material cover	Plastic, transparent
Material	Aluminium / polycarbonate
Colour	White / aluminium
Length (mm)	381
Width (mm)	170
Height/depth (mm)	75
Nominal voltage (V)	24
Voltage type	AC/DC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	1
Number of lamps	2
Light output in emergency operation (lm)	89
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	73
Protection class	II
Degree of protection (IP)	65
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Only single-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	25
Circuit	Other
Impact strength (IK)	10
Power consumption maintained mode (W)	9,2
Apparent power consumption maintained mode (VA)	14,1

Temperature range (°C) ~25 ~ +35

**Article Details**

Product class	Emergency luminaire
E-code	EC001957
Discount group	30401
Harmonized code	9405409100
GLN	8713812000008

**Ordering information**

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

**Supply Information**

Weight (kg)	1,495
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	426 x 188 x 111