



WER 02/HF

Slave 2 watt, 230 Volt surface mount led luminaire, series Alulux

Product Information

Type	WER 02/HF
Catalog number	11230055
Category_	Escape route signalisation
GTIN	08713812752471
GID	7TCA091130R0020
Serie	Alulux
Warranty (Year)	5



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Wall
Mounting form	Surface
Material housing	Aluminium
Colour housing	Aluminium
Material cover	Plastic, opal
Material	Aluminium
Colour	Aluminium
Length (mm)	490
Width (mm)	140
Height/depth (mm)	60
Nominal voltage (V)	230
Voltage type	AC/DC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	60
Protection class	I
Degree of protection (IP)	20
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	25
Circuit	Other
Power consumption maintained mode (W)	6
Apparent power consumption maintained mode (VA)	13,8
Nominal current (mA)	60
Inrush Current (A - 0.1ms)	16
Powerfactor	0,6
Temperature range (°C)	5 ~ +25

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	1,3
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	492 x 147 x 62