



EVA-V-CWI-X/ZWART

Slave 2 watt, designed for mounting from 4 meter upwards, 230 Volt square black recess led luminaire, series Evago Light distribution: wide (W)

Product Information

Type	EVA-V-CWI-X/ZWART
Catalog number	5530257079
Category_	Escape route lighting
GTIN	08713812770482
GID	7TCA091130R0571
Serie	Evago
Warranty (Year)	5
Other	With the additional lens the luminaire can be mounted from > 8 meter and up



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Recess
Material housing	Aluminium / plastic
Colour housing	Black
Material	Aluminium / polycarbonate
Colour	Black
Length (mm)	226
Width (mm)	100
Height/depth (mm)	38
Maximum outer diameter (mm)	100
Built-in length (mm)	226
Built-in width (mm)	68
Built-in diameter (mm)	68
Built-in depth (mm)	35
Nominal voltage (V)	230
Voltage type	AC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Light output in emergency operation (lm)	238
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5600
CRI	70
Protection class	II
Degree of protection (IP)	42
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Power consumption maintained mode (W)	5
Apparent power consumption maintained	

Apparent power consumption maintenance mode (VA)	5,5
Nominal current (mA)	24
Inrush Current (A - 0.1ms)	3
Powerfactor	0,9
Temperature range (°C)	0 ~ +40

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	0,321
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	225 x 170 x 62