

PRODUCT SPECIFICATION

EGR1LS1D-S22

Guideway 230v AC 22M IP40 Recess

Catalogue Number **EGR1LS1D-S22**
 GID **7TCA091130R0406**
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Mains / Slave Operation**
 Mounting Method/Form **Ceiling, Wall Recessed**
 Housing Material **Aluminium/Plastic**
 Colour **Silver**
 Dimensions (LxWxD) **235 x 84 x 134 mm**
 Temperature Range **5 to 35°C**
 Weight **1.2 Kg**

Emergency Duration (Hours) **Mains / Central Battery**
 Battery **Mains / Central Battery**
 Monitoring Equipment **None**
 Lamp **1 x 2W LED**
 Emergency Light Output (Lumens) **Not Applicable**
 Average Lifespan light source (Hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 5000 / 80**
 Degree of Protection **IP40**

Type of Legend **Single or Double Sided**
 Exit Sign Viewing/Recognition Distance (m) **22**
 Nominal Voltage **220-240v AC/DC 0-60Hz**
 Power Consumption **4.4 VA / 4 Watts**
 Current **Nominal: 19mA (mA)**

Accessories

XEN2EG22 Down ISO7010 Legend Single Sided
XEN3EG22 Left ISO7010 Legend Single Sided
XEN6EG22 Right ISO7010 Legend Single Sided
XEN5EG22 Up ISO7010 Legend Single Sided
XBN1EG22 Arabic English Legend Single Sided
XEN0G22 Blank Legend Single Sided

EG-T4EG Cover Discs (2x semi-circular, 2x rectangular) for Slave

EG-TKIT50 Suspension Kit Pendant 50mm
EG-TKIT100 Suspension Kit Pendant 100mm
EG-WKIT150 Wire Suspension Kit 150mm

XEN602EG22 Down ISO7010 Legend Flag Mount
XEN603EG22 Left ISO7010 Legend Flag Mount
XEN606EG22 Right ISO7010 Legend Flag Mount
XEN605EG22 Up ISO7010 Legend Flag Mount



Exit Sign Suspended
 EGR1LS1D-S22 + EG-WKIT150



Exit Sign Recessed
 EGR1LS1D-S22

