



中国国家强制性产品认证证书

证书编号：2024010302646952

认证委托人名称及地址

ABB S. P. A.

via Pescaria 5, 24123 Bergamo Italy

生产者名称及地址

ABB S. P. A.

via Pescaria 5, 24123 Bergamo Italy

生产企业名称及地址

ABB S. P. A.

Via Enrico Fermi 14, IT-03100 Frosinone Italy

产品名称和系列、型号、规格

隔离开关

T6D 800 PV, T6N-D/PV 600, T6N-D/PV 800; 详见附页

产品标准和技术要求

GB/T 14048.3-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2024 年 06 月 25 日 有效期至：2029 年 06 月 24 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





中国国家强制性产品认证证书

证书编号: 2024010302646952

证书附页: 第 1 页 共 2 页

型号: T6D 800 PV, T6N-D/PV 600, T6N-D/PV 800

额定冲击耐受电压 (U_{imp}): 8kV;

额定绝缘电压(U_i): 1150V

约定发热电流(I_{th}): T6D 800 PV, T6N-D/PV 800:800A; T6N-D/PV 600:600A

额定工作电压(U_e): DC1100V


额定工作电流(I_e): T6D 800 PV:800A; T6N-D/PV 600, T6N-D/PV 800:600A,800A

额定短时耐受电流(I_{cw}): 9.6kA/1s

额定短时接通能力(I_{cm}): 9.6kA

使用类别: DC-22B, DC-PV2

直流接线方式:



本页为证书附页，应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE


中国质量认证中心有限公司




中国国家强制性产品认证证书

证书编号: 2024010302646952

证书附页: 第 2 页 共 2 页



型号解释:



本页为证书附页，应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010302646952

NAME AND ADDRESS OF THE APPLICANT

ABB S.P.A.

via Pescaria 5, 24123 Bergamo Italy

NAME AND ADDRESS OF THE MANUFACTURER

ABB S.P.A.

via Pescaria 5, 24123 Bergamo Italy

NAME AND LOCATION OF THE FACTORY

ABB S.P.A.

Via Enrico Fermi 14, IT-03100 Frosinone Italy

PRODUCT NAME,MODEL AND SPECIFICATION

Switch-disconnector

T6D 800 PV, T6N-D/PV 600, T6N-D/PV 800;See the appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.3-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jun.25,2024

Valid until: Jun.24,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010302646952

Appendix: Page 1 of 1

T6D 800 PV, T6N-D/PV 600, T6N-D/PV 800

Uimp: 8kV;

Ui: 1150V

Ith: T6D 800 PV, T6N-D/PV 800:800A; T6N-D/PV 600:600A


Ue: DC1100V

Ie: T6D 800 PV:800A; T6N-D/PV 600, T6N-D/PV 800:600A,800A

Icw: 9.6kA/1s

Icm: 9.6kA

Utilization Category: DC-22B, DC-PV2



This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.