



<p>Number of Poles 1 & 2</p>	<p>Molded Case Circuit Breakers Q-Line: 15A to 30A</p>		
<p>Voltage Rating 120Vac 120/240Vac</p>	<p>Type Thermal Magnetic: THQL, THHQL, THQLT, THQLQ, THQP, THQB, THHQB, THQC, THHQC</p>		<p>Adjustments Long-time delay thermal trip: not adjustable. Instantaneous magnetic trip: not adjustable.</p>
<p>Current Rating 15A to 30A</p>	<p>eMCB: THQL, THHQL, THQB, THHQB, THQC, THHQC</p>		
<p>Protection Thermal Magnetic Combination Arc Fault Ground Fault Personnel Protection Ground Fault Equipment Protection Dual Function</p>	<p>Operating Conditions: Curve represents cold trip with no prior load. Curves apply at 60 Hertz with reference ambient temperature of 40°C wired with conductors of corresponding rating. Refer to technical guide from the UL catalog for more information regarding thermal application.</p>		