

PRODUCT SPECIFICATION

SR2-SA230LT-EF1

Serenga 2 230v AC Open Area 4-12m IP54 EMEX Test Surface

Catalogue Number **SR2-SA230LT-EF1**
 GID **7TCA091140R0401**
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Mains / Slave Operation**
 Mounting Method/Form **Ceiling Surface**
 Housing Material **Aluminium/Plastic**
 Colour **White**
 Dimensions (LxWxD) **150 x 150 x 35 mm**
 Temperature Range **0 to 40°C**
 Weight **0.745 Kg**

Nominal Voltage **220-240v AC 50/60Hz**
 Emergency Duration (Hours) **Mains / Central Battery Hours**
 Battery **Mains / Central Battery**
 Monitoring Equipment **EMEX test**
 Lamp **1 x 2W LED**
 Light output in Emergency Operation **203 Lumens**
 Average Lifespan light source (hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 5600 / 70**
 Degree of Protection **IP 54 IK tbc**

Wiring System **Mains / CBU**
 Type of Legend **Not Applicable**
 Exit Sign Viewing/Recognition Distance (m) **Not Applicable**
 Power Consumption **5.5 VA / 5 Watts**
 Nominal Current **24 (mA)**
 Inrush Current **tbc A to 0.1 ms**

Accessories

- SR2-LENS1** Lens A Escape route 2-4M Ceiling mount
- SR2-LENS2** Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M Ceiling mount
- SR2-LENS3** Lens C Escape route 8-12M Ceiling mount
- SR2-LENS4** Lens D Open Area 2-4M Ceiling mount
- SR2-LENS5** Lens E Open Area 4-8M Ceiling mount
- SR2-LENS6** Lens E Open Area 8-12M Ceiling mount
- SR2-LENS7** Lens G Escape route 2-4M Wall mount

