TYPICAL WIRING DIAGRAM



USE COPPER WIRE ONLY

USE ONLY 60 DEG.C (140 DEG.F) CONDUCTORS ON ALL FIELD INSTALLED LINE, LOAD AND NEUTRAL TERMINATIONS.

WIRE RANGE		
CONNECTOR	COPPER	
	SOLID	STRANDED
LINE-7310	14-10	14-10
LOAD-PLUG	—	—
NEUTRAL-7310	14-10	14-10
EQUIP.GRD.-GL2	12-8	12-2

LUG TIGHTENING TORQUE (LB-IN)

SCREW TYPE	WIRE SIZE	TORQUE
SLOT	14-10	32-35
	8	36-40
	6-4	41-45
	3-2/0	45-50

RAINPROOF POWER OUTLET

MODEL NO. U023

20 AMPS
120/240 VOLTS A-C
TYPE 3R ENCLOSURE

WHEN CABINET HAS PROVISION FOR A CONDUIT HUB, SELECT FROM CHART BELOW.

CONDUIT SIZE	CLOSURE CAP	3/4	1	1 1/4	1 1/2
CAT. NO.	801	807	810	812	815

DANGER

HAZARD OF ELECTRICAL SHOCK OR BURN. TURN OFF POWER BEFORE WORKING INSIDE THIS EQUIPMENT.

MIDWEST ELECTRIC PRODUCTS,INC.
P.O. BOX 910
MANKATO, MN 56002-0910
WWW.MIDWESTELECTRIC.COM

MNP600003

Midwest®