



中国国家强制性产品认证证书

证书编号: 2012010304589737

委托人名称、地址

ABB France

3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

生产者(制造商)名称、地址

ABB France

3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

生产企业名称、地址

ABB 新会低压开关有限公司

广东省江门市新会区今古洲工业开发区

产品名称和系列、规格、型号

接触器

AF40-30-□□-□□, AF52-30-□□-□□, AF65-30-□□-□□; 详见附件

产品标准和技术要求

GB/T14048.4-2010

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求,
特发此证。

发证日期: 2017 年 06 月 21 日 有效期至: 2022 年 06 月 21 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2012 年 12 月 31 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



主 任:



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2012010304589737

NAME AND ADDRESS OF THE APPLICANT

ABB France
3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

NAME AND ADDRESS OF THE MANUFACTURER

ABB France
3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

NAME AND ADDRESS OF THE FACTORY

ABB Xinhui Low Voltage Switchgear Co., Ltd.
Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen, Guangdong Province,
P.R.China

PRODUCT NAME, MODEL AND SPECIFICATION

contactor
AF40-30-□□-□□, AF52-30-□□-□□, AF65-30-□□-□□; see the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T14048.4-2010

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

Valid from: Jun.21,2017

Valid until: Jun.21,2022

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Dec.31,2012

The certificate information is available through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

附录:

第 1 页 共 5 页

证书编号: 2012010304589737

纸号: 1734908

型号: AF40-30-□□-□□, AF52-30-□□-□□, AF65-30-□□-□□;

I_{in} : 105A;

U_i : 690V;

I_s : AC690V/80kA;

防护等级: IP10;

U_e : AC24-60V、DC20-60V、AC/DC48-130V、AC/DC100-250V、AC/DC250-500V;

极数: 3P;

使用类别、 U_e 、 I_e :

使用类别	U_e (V)	I_e (A)		
		AF40	AF52	AF65
AC-1	690	70	100	105
AC-3	220-230-240	40	53	65
AC-3	380-400	40	53	65
AC-3	415	40	53	65
AC-3	440	40	53	65
AC-3	500	35	45	55
AC-3	690	25	35	39
AC-4	220-500	35	45	52
AC-4	690	25	28	31
AC-8a	400	53	70	85

注: 此附录与证书同时使用时有效。



主任:



中国质量认证中心



中国国家强制性产品认证证书

附录:

第 2 页 共 5 页

证书编号: 2012010304589737

纸号: 1734908

配用的辅助触头:

型号: CAL4-11、CA4-22E;

触头种类和对数: CAL4-11: X、Y 型, 1N01NC; CA4-22E: X、Y 型, 2N02NC;

I_{th} : 16A;

使用类别、 U_c 、 I_c :

CAL4-11	AC-15 额定 (V)	(A)	DC-13 额定 (V)	(A)
	127	6	24	6
	240	4	48	4
	400	3	72	1
	440	3	125	0.55
	500	2	250	0.27
	690	2	400	0.15
			500	0.13
			600	0.1
CA4-22E	AC-15 额定 (V)	(A)	DC-13 额定 (V)	(A)
	24-127	6	24	6
	220-240	4	48	4
	380-440	3	72	1
	500-690	2	110-125	0.55
			220-250	0.27
			400	0.15
			500	0.13
			600	0.1

注: 此附录与证书同时使用时有效。



主任:



中国质量认证中心



中国国家强制性产品认证证书

附录:

第 3 页 共 5 页

证书编号: 2012010304589737

纸号: 1734908

型号的解释:

型号的解释:

AF □□ - 3 0 - □□ - □□

控制线圈型号: 见表一

附件种类数量: 00: 没有附加附件

11: 附加一只附件 CAL4-11

22: 附加一只附件 CA4-22E

常闭主触点对数 0: 0 对常闭主触点

常开主触点对数 3: 3 对常开主触点

400V, AC-3 使用类别下额定工作电流:
40:40A, 52:53A, 65:65A,

系列名称: AF 系列接触器

CAL4-11 和 CA4-22E 附件为辅助触头。

注: 此附录与证书同时使用时有效。



主任:



中国质量认证中心



中国国家强制性产品认证证书

附录:

第 4 页 共 5 页

证书编号: 2012010304589737

纸号: 1734908

型号的解释: (续)

所有产品型号	控制线圈电压	所有产品型号	控制线圈电压
AF40-30-00-11	24-60V50/60Hz DC20-60V	AF65-30-00-11	24-60V50/60Hz DC20-60V
AF40-30-00-12	48-130V50/60Hz -DC	AF65-30-00-12	48-130V50/60Hz-DC
AF40-30-00-13	100-250V50/60Hz-DC	AF65-30-00-13	100-250V50/60Hz-DC
AF40-30-00-14	250-500V50/60Hz-DC	AF65-30-00-14	250-500V50/60Hz-DC
AF40-30-11-11	24-60V50/60Hz DC20-60V	AF65-30-11-11	24-60V50/60Hz DC20-60V
AF40-30-11-12	48-130V50/60Hz-DC	AF65-30-11-12	48-130V50/60Hz-DC
AF40-30-11-13	100-250V50/60Hz-DC	AF65-30-11-13	100-250V50/60Hz-DC
AF40-30-11-14	250-500V50/60Hz-DC	AF65-30-11-14	250-500V50/60Hz-DC
AF40-30-22-11	24-60V50/60Hz DC20-60V	AF65-30-22-11	24-60V50/60Hz DC20-60V
AF40-30-22-12	48-130V50/60Hz-DC	AF65-30-22-12	48-130V50/60Hz-DC
AF40-30-22-13	100-250V50/60Hz-DC	AF65-30-22-13	100-250V50/60Hz-DC
AF40-30-22-14	250-500V50/60Hz-DC	AF65-30-22-14	250-500V50/60Hz-DC
AF52-30-00-11	24-60V50/60Hz DC20-60V	AF40-30-00-41	24-60V50/60Hz
AF52-30-00-12	48-130V50/60Hz-DC	AF40-30-11-41	24-60V50/60Hz
AF52-30-00-13	100-250V50/60Hz-DC	AF40-30-22-41	24-60V50/60Hz
AF52-30-00-14	250-500V50/60Hz-DC	AF52-30-00-41	24-60V50/60Hz
AF52-30-11-11	24-60V50/60Hz DC20-60V	AF52-30-11-41	24-60V50/60Hz

注: 此附录与证书同时使用时有效。



主 任:



中国质量认证中心



中国国家强制性产品认证证书

附录:

第 5 页 共 5 页

证书编号: 2012010304589737

纸号: 1734908

型号的解释: (续)

AF52-30-11-12	48-130V50/60Hz-DC	AF52-30-22-41	24-60V50/60Hz
AF52-30-11-13	100-250V50/60Hz-DC	AF65-30-00-41	24-60V50/60Hz
AF52-30-11-14	250-500V50/60Hz-DC	AF65-30-11-41	24-60V50/60Hz
AF52-30-22-11	24-60V50/60Hz DC20-60V	AF65-30-22-41	24-60V50/60Hz
AF52-30-22-12	48-130V50/60Hz-DC		
AF52-30-22-13	100-250V50/60Hz-DC		
AF52-30-22-14	250-500V50/60Hz-DC		

注: 此附录与证书同时使用时有效。



主 任:



中国质量认证中心