

JULY 2023

Hazlux® Hotsheet

Quick-ship program



H3 LED Series

Complete fixture, with ceiling mount

Class 1 Div 2 area lighting, 120-277, 5000K, TG (Type 5), gray

DL005EUN0TGC2EGU 37W, with 3/4" Ceiling mount/pendant

DL007EUN0TGC2EGU 48W, with 3/4" Ceiling mount/pendant

DL010EUN0TGC2EGU 74W, with 3/4" Ceiling mount/pendant

DL015EUN0TGC2EGU 103W, with 3/4" Ceiling mount/pendant

DL017EUN0TGC2EGU 115W, with 3/4" Ceiling mount/pendant

DL020EUN0TGC2EGU 138W, with 3/4" Ceiling mount/pendant

Fixture assembly less mounting

DL010EUN0TGEU 74W, mounting must be selected

VB2-VIBG 3/4" Wall mount

VA2G 3/4" Cone-top pendant

HV3G Hazvertor™ adaptor ring Crouse-Hinds ceiling, pendant & straight stanchion top hats

Accessories

VGU22G Cast aluminum guard

AH1 Series



Pendant mount
(included standard)



Fixture

AH161K5R51TGPGU= Class 1 Div 1 area lighting, 60 watt, 120-277, 5000K, R5, clear glass, pendant mount, gray

PB02= Wall/pipe U-bracket

PC01= Pipe clamp (M8*48mm) for pole Ø 1-7/8" (48mm)

PC02= Pipe clamp (M8*60mm) for pole Ø 2-3/8" (60mm)

WG04= Wire guard (stainless steel)

FC Series



Pendant mount
(included standard)



Fixture

FC151K5W1TGPGU= Hazlux flood light LED 150 watts, 120-277, 5000K, 120°, Class 1 Div 1, clear glass, pendant mount, gray

FC151K5W2TGPGU= Hazlux flood light LED 150 watts, 120-277, 5000K, 120°, Class 1 Div 2, clear glass, pendant mount, gray

SN01= Pole type stanchion

UB01= Yoke/pipe bracket

UB03= Anti-vibration U-bracket

WG01= Stainless steel wire guard



JULY 2023


Hazlux® Hotsheet

Quick-ship program

LI1 Series



Pendant mount
(included standard)



Fixture

LI181K5WTGPGU= Hazlux linear light LED, 80 watt, 120-277, 5000K, 110°, clear glass, pendant mount, gray

PC01= Pipe clamp (M8*48mm) for pole Ø 1-7/8" (48mm)

PC02= Pipe clamp (M8*60mm) for pole Ø 2-3/8" (60mm)

SC04= Stainless steel safety cable kit

UB02= Yoke/pipe bracket (SUS 304) stainless steel

LI1-EM Series



Pendant mount
(included standard)



Fixture

LI181K5WTGUGEMU= Hazlux linear light LED, 80 watt, 120-277, 5000K, 110°, clear glass, pendant mount + yoke bracket, gray, 90 mins emergency

PC01= Pipe clamp (M8*48mm) for pole Ø 1-7/8" (48mm)

PC02= Pipe clamp (M8*60mm) for pole Ø 2-3/8" (60mm)

SC04= Stainless steel safety cable kit

Non-hazardous rated test switch included

LE2 Series



Pendant mount
(included standard)



Fixture

LE241K5WCPGU= Hazlux linear light LED, 40 watt, 120-277, 5000K, 110°, clear polycarbonate, pendant mount, gray

PC01= Pipe clamp (M8*48mm) for pole Ø 1-7/8" (48mm)

PC02= Pipe clamp (M8*60mm) for pole Ø 2-3/8" (60mm)

SC02= Stainless steel safety cable kit

UB02= Yoke/pipe bracket (SUS 304) stainless steel

When ordering, please use quote # **HOTSHEET**

