

PRODUCT SPECIFICATION

# SR2-SW230-G1

## Serenga 2 230v AC IP54 Wall Surface

Catalogue Number **SR2-SW230-G1**  
GID **7TCA091130R0472**  
Warranty **4 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Mains / Slave Operation**  
Mounting Method/Form **Ceiling Surface**  
Housing Material **Aluminium/Plastic**  
Colour **White**  
Dimensions (LxWxD) **150 x 150 x 35 mm**  
Temperature Range **0 to 40°C**  
Weight **0.745 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**  
Battery **Mains / Central Battery**  
Monitoring Equipment **None**  
Lamp **1 x 2W LED**  
Emergency Light Output (Lumens) **203**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 5600 / 70**  
Degree of Protection **IP54**

Type of Legend **Not Applicable**  
Exit Sign Viewing/Recognition Distance (m) **Not Applicable**  
Nominal Voltage **220-240v AC 50/60Hz**  
Power Consumption **5.5 VA / 5 Watts**  
Current **Nominal: 24mA (mA)**

### Accessories

- SR2-LENS1** Lens A Escape route 2-4M Ceiling mount
- SR2-LENS2** Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M Ceiling mount
- SR2-LENS3** Lens C Escape route 8-12M Ceiling mount
- SR2-LENS4** Lens D Open Area 2-4M Ceiling mount
- SR2-LENS5** Lens E Open Area 4-8M Ceiling mount
- SR2-LENS6** Lens E Open Area 8-12M Ceiling mount
- SR2-LENS7** Lens G Escape route 2-4M Wall mount

