

PRODUCT SPECIFICATION

# OZD3LS61

## Horizon Self-Contained 25M IP20 Self-Test Recess

Catalogue Number **OZD3LS61**

GID **7TCA091160R0202**

Warranty **3 Year/s Refer to ABB warranty terms & conditions**

Power Supply System **Self-Contained (individual battery)**

Mounting Method/Form **Ceiling Surface**

Housing Material **Aluminium/Plastic**

Colour **White/Silver**

Dimensions (LxWxD) **364 x 167 x 82 mm**

Temperature Range **0 to 25°C**

Weight **1.3 Kg**

Emergency Duration (Hours) **3 Hours**

Battery **NiCd**

Monitoring Equipment **Automatic self test**

Lamp **2 x 2W LED**

Emergency Light Output (Lumens) **Not Applicable**

Average Lifespan light source (Hours) **100000 Hours**

Light Colour/Temperature/CRI **White / 6350 / 73**

Degree of Protection **IP40**

Type of Legend **Single or Double Sided (Order separate)**

Exit Sign Viewing/Recognition Distance (m) **25**

Nominal Voltage **220-240v AC 50Hz**

Power Consumption **9.9 VA / 5.1 Watts**

Current **Nominal: 42.5mA (mA) Inrush: 18A**

### Accessories

**XEN20HS** Single Sided Down ISO7010 Legend

**XEN30HS** Single Sided Left ISO7010 Legend

**XEN60HS** Single Sided Right ISO7010 Legend

**XEN50HS** Single Sided Up ISO7010 Legend

**XB01HS** Single Sided Arabic English Legend

**XLF802HS** Fire Extinguisher Legend

**XLF803HS** Hose Reel Legend

**XEN22HD** Double Sided Down+Down ISO7010 Legend

**XEN36HD** Double Sided Left+Right ISO7010 Legend

**XEN55HD** Double Sided Up+Up ISO7010 Legend



Exit sign  
OZD3LS61 + XEN20HS

