



# EC DECLARATION OF CONFORMITY

(supplier's name) We ABB SACE S.p.A

(address) VIALE VICENZA, 61

36063 - MAROSTICA (VI)

declare under our sole responsibility that the product : \_\_\_\_\_

THERMOPLASTIC WIRING DUCTS WITH VERTICAL SLOTS - 05 SERIES

(name,type or model,lot,batch or serial number,possibly sources and numbers of items)

ARTICLES : IN ATTACHED

to which this declaration relates is in conformity with the following standard(s) or other  
normative/documents EN 50085-2-3

RELEASE FROM IMQ INSTITUTE BY D.A.T. N° CA02.00382

(title and/or number and date of issue of the standard(s) or other normative document(s))

following the provisions of the Directive(s) 73/23 CEE MODIFIED BY 93/68 CEE

MAROSTICA, 11/03/2002

(Place and date of issue)

02

(last two digits of the year in which the mark was affixed)

ABB SACE S.p.A  
TECHNICAL MANAGER  
ENZO RIZZI

(seal, name and signature of authorized person)

Mod. 379 - 12/94 - 900

1SLT000009D00

# Wiring ducts

## Thermoplastic wiring ducts with vertical slots



Article	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-metres
---------	---------------------	---------------	------------------

### Wiring duct with 8/12 mm slots

05 019	15x17	0.06	92
05 033	25x30	0.21	116
05 035	40x30	0.27	80
05 037	60x30	0.38	52
05 043	25x40	0.25	96
05 045	40x40	0.31	60
05 047	60x40	0.46	40
05 049	80x40	0.47	32
05 051	100x40	0.55	24
05 053	120x40	0.65	20
05 063	25x60	0.24	68
05 065	40x60	0.34	44
05 067	60x60	0.47	32
05 069	80x60	0.52	24
05 071	100x60	0.59	18
05 073	120x60	0.73	14
05 083	25x80	0.29	56
05 085	40x80	0.38	36
05 087	60x80	0.50	24
05 089	80x80	0.59	16
05 091	100x80	0.68	16
05 093	120x80	0.89	12
05 094	25x100	0.46	40
05 095	40x100	0.53	28
05 096	60x100	0.73	20
05 097	80x100	0.91	14
05 098	100x100	1.06	8
05 099	150x100	1.37	8

### Wiring duct with 4/6 mm slots

05 119	15x17	0.06	92
05 133	25x30	0.21	116
05 135	40x30	0.27	80
05 137	60x30	0.38	52
05 143	25x40	0.25	96
05 145	40x40	0.31	60
05 147	60x40	0.46	40
05 149	80x40	0.47	32
05 151	100x40	0.55	24
05 153	120x40	0.65	20
05 163	25x60	0.24	68
05 165	40x60	0.34	44
05 167	60x60	0.47	32
05 169	80x60	0.52	24
05 171	100x60	0.59	18
05 173	120x60	0.73	14
05 183	25x80	0.29	56
05 185	40x80	0.38	36
05 187	60x80	0.50	24
05 189	80x80	0.59	16
05 191	100x80	0.68	16
05 193	120x80	0.89	12
05 194	25x100	0.46	40
05 195	40x100	0.53	28
05 196	60x100	0.73	20
05 197	80x100	0.91	14
05 198	100x100	1.06	8
05 199	150x100	1.37	8

Overall dimensions ..... pages 11/24 - 11/27

# Wiring ducts

## Thermoplastic wiring ducts with vertical slots



Article	Description (mm)	Unit/pack-pieces
---------	------------------	------------------

### Fix-O-rapid


Rapid clip for DIN rail

05 250	Trunking base 25	20/600
05 252	Trunking base 40	20/600
05 254	Trunking base 60	20/600
05 256	Trunking base 80	20/240
05 258	Trunking base 100	20/240
05 260	Trunking base 120	20/240
05 262	Trunking base 150	20/240

Rapid clip for base plate

05 270	Trunking base 25	20/600
05 272	Trunking base 40	20/600
05 274	Trunking base 60	20/600
05 276	Trunking base 80	20/240
05 278	Trunking base 100	20/240
05 280	Trunking base 120	20/240
05 282	Trunking base 150	20/240

Can be snapped onto holes as shown:




### Spare covers

2-metre length

05 300	Trunking base 15	2/200
05 302	Trunking base 25	2/60
05 304	Trunking base 40	2/40
05 306	Trunking base 60	2/24
05 308	Trunking base 80	2/16
05 310	Trunking base 100	2/48
05 312	Trunking base 120	2/36
05 314	Trunking base 150	2/28

# Wiring ducts

## Thermoplastic wiring ducts with vertical slots



Article	Description (mm)	Unit/pack-pieces
---------	------------------	------------------

### Duct shears

05 265		1
--------	--	---

### Rivet fastener

05 266	For ø 4 and 6mm rivets	1/12
--------	------------------------	------

### Plastic rivet

05 214	Ø 4 mm	100
05 216	Ø 6 mm	100

### Plastic cable retainer

Suitable for wiring ducts with 8/12 mm slots only.

05 224	Trunking base 40	100
05 226	Trunking base 60	100
05 228	Trunking base 80	100
05 230	Trunking base 100/120	100

### Plastic label tag

Suitable for wiring ducts with 8/12 mm slots only.

05 240		100
--------	--	-----