


# Earth bonds & clamps

## Earth bars



### Standards

BS 7430

### Earth bar

Part no.	Description	Length (mm)	Weight each (kg)
<b>Copper earth bar</b>			
LK245-6	6 way	400	1.80
LK245-8	8 way	500	2.20
LK245-10	10 way	650	2.80
LK245-12	12 way	750	3.20
LK245-14	14 way	850	3.60
LK245-16	16 way	950	4.00
LK245-18	18 way	1050	4.40
LK245-20	20 way	1200	5.00
LK245-22	22 way	1300	5.40
LK245-24	24 way	1400	5.80
LK245-26	26 way	1500	6.20
LK245-28	28 way	1650	6.90
LK245-30	30 way	1750	7.30
<b>Tinned copper earth bar</b>			
LK245-6-T	6 way	400	1.80
LK245-8-T	8 way	500	2.20
LK245-10-T	10 way	650	2.80
LK245-12-T	12 way	750	3.20
LK245-14-T	14 way	850	3.60
LK245-16-T	16 way	950	4.00
LK245-18-T	18 way	1050	4.40
LK245-20-T	20 way	1200	5.00
LK245-22-T	22 way	1300	5.40
LK245-24-T	24 way	1400	5.80
LK245-26-T	26 way	1500	6.20
LK245-28-T	28 way	1650	6.90
LK245-30-T	30 way	1750	7.30

– Fix using countersunk wood screws 1½" No. 12 (Part no. SW110) and wall plugs (Part no. PS310)

– Standard width x height: 90 mm x 77 mm