



$S = \begin{cases} \text{Ø7} - \text{Special IM 3001/*11} \\ \text{M6} - \text{Special IM 3601/*11} \end{cases}$
M2AA 080

Additional information:
 VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador
 VC219: Flange ring FT 100 / Aro brida FT 100 // VC220: Flange ring FF 100 / Aro brida FF 100

Motor Dimension Print		Motor Type : M2AA 080	Document Nº : 3GZE 500 082-921.005
Description : Motor flange mounted special (2-pieces) IM3001/*11 or IM3601/*11 Motor con brida (2 piezas) IM3001/*11 o IM3601/*11			
Unit : Discret Automation & Motion - Fábrica Motores	Issued by : ERM/ A. Caubera	Replaces :	
Date : 2012-11-29	Approved by : ERM/ G. Blanes	Replaced by :	
Asea Brown Boveri, S.A.	Customer Reference :		ABB