

产品认证证书

II型自愿认证

证书编号: CQC2004010305127663

发证日期: 2021年02月01日

有效期至: 2031年02月01日

委托人名称 ABB France
及注册地址 2 rue d'Arsonval 69680 Chassieu France

制造商名称 ABB France
及注册地址 2 rue d'Arsonval 69680 Chassieu France

生产企业名称 COMEPI s.r.l
及生产地址 Via Novarino 23899 Robbiate (Lc) Italy

产品名称和系列、规格、型号 行程开关
LS;Ui:690V;Uimp:6kV;AC-15:Ue/Ie:AC240V/3A;DC-13:Ue/Ie:DC250V/0.27A,DC24V/2.8A
; Ith:10A;IP65;型号解释见附件

产品标准和技术要求 GB/T 14048.5-2017

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人:

主任:

陈昕 陆楠

中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0005116

PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2004010305127663

Valid from: Feb.01,2021

Valid until: Feb.01,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND LOCATION OF THE FACTORY COMEPI s.r.l
Via Novarino 23899 Robbiate (Lc) Italy

PRODUCT NAME, MODEL AND SPECIFICATION Limit Switch
LS;Ui:690V;Uimp:6kV;AC-15:Ue/Ie:AC240V/3A;DC-13:Ue/Ie:DC250V/0.27A,DC24V/2.8A;
Ith:10A;IP65;See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 14048.5-2017

TYPE OF CERTIFICATION SCHEMES Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.
The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNED BY:

陈昕

PRESIDENT:

陆楠

CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C(2) 0005116

产品认证证书

II型自愿认证

附 录

证书编号: CQC2004010305127663

第 1 页 共 2 页

纸 号: 5116

型号解释:

LS 30 P 31 C 11
1 2 3 4 5 6

1- Basic type 型号系列为 LS

2- Casing width 外壳宽度

30= 30 mm width +1 cable inlet for Pg 13.5 cable gland

30= 外壳宽度 30 mm +1 Pg 13.5 导线接线口

31= 30 mm width +1 cable inlet for Pg 11 cable gland

31= 外壳宽度 30 mm +1 Pg 11 导线接线口

40= 40 mm width +1 cable inlet for Pg 13.5 cable gland

40= 外壳宽度 40 mm +1 Pg 13.5 导线接线口

3- Plastic casing 塑料外壳

4- Operating heads code 操作头形式代码

11=Plain plunger 平顶柱塞式

13=Roller plunger 滚轮柱塞式

31=Roller leve 31 滚轮杠杆式

41=Roller lever 41 型号滚轮杠杆式

51=Adjustable roller lever 可调节滚轮杠杆式

注: 此附录与证书同时使用时有效。



中国质量认证中心

产品认证证书

II型自愿认证

附 录

证书编号: CQC2004010305127663

第 2 页 共 2 页

纸 号: 5116

5- Action type 动作形式

B: zb Snap action 快动式

L: zb Slow action (contact dependent) 缓动式

D: zb Slow action non-overlapping late make 缓动无重叠

C: zb Slow action overlapping early make zb 缓动有重叠

6- Contact block 触点构成

11: 1NO contact + 1NC contact 1 常开 ; 1 常闭

20: 2NO contacts 2 常开 ; 0 常闭

02: 2NC contacts 0 常开 ; 2 常闭

注: 此附录与证书同时使用时有效。



中国质量认证中心