

1) Short

2) Large

S = { Ø15 – Special IM 2001/\*11  
M12 – Special IM 2101/\*11

## M2AA 132

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador


VC243: Flange ring FF 215 / Aro brida FF 215 // VC244: Flange ring FT215 / Aro brida FT 215

### Motor Dimension Print

Motor Type :  
M2AA 132 Short

Document Nº :  
3GZE 500 130-961.005

Description : Motor foot and flange mounted special (2-pieces) IM2001/\*11 or IM2101/\*11  
Motor con patas y brida (2 piezas) IM2001/\*11 o IM2101/\*11



Unit : Discret Automation & Motion - Fábrica Motores  
Date : 2012-12-13

Issued by : ERM/ A. Caubera  
Approved by : ERM/ G. Blanes

Replaces :  
Replaced by :

**Asea Brown Boveri, S.A**

Customer Reference :

**ABB**