



Tmax

DOC. N.° 1SDH000436R0825 - L9228

FC Cu - Terminali anteriori per cavi in rame T4-T5 fisso
 FC Cu - Front terminals for copper cables T4-T5 fixed
 FC Cu - Vorderseitige Anschlüsse für Kupferkabel T4-T5 fest
 FC Cu - Prises avant pour câbles en cuivre T4-T5 fixe
 FC Cu - Terminales frontales para cables de cobre T4-T5 fijo
 FC Cu - 铜电缆前接线端子 T4-T5 固定式


T4		T5	
III	3(6) 3(6)	III	3(6) 3(6)
IV	4(8) 4(8)	IV	4(8) 4(8)

T5 70 mm ²		T5 240 mm ²	
III	IV		
1(2)	1(2)		
3(6)	4(8)		
1(2)	-		
-	1(2)		
3(6)	4(8)		
3(6)	4(8)		
2(4)	2(4)		
4(8)	4(8)		
2(4)	2(4)		
3(6)	4(8)		



C

1 2



T4

MAX 最大 185 mm² MAX 最大 120 mm²

MIN 最小 2,5 mm² MIN 最小 2,5 mm²


T5

MAX 最大 300 mm² MAX 最大 240 mm²

MIN 最小 16 mm² MIN 最小 16 mm²


D

T5




E

T5




F

T5




G

T5 III



I

T5 IV




ABB

<http://www.abb.com>

J



T5

	A	B	C
	Min (mm)	Min (mm)	ø Max (mm)
240 mm ²	22,5	56,5	21,5
70 mm ²	22,5	56,5	13



K

3



T5
240mm²

MAX 最大 240 mm²
MIN 最小 120 mm²

T5
70mm²

MAX 最大 70 mm²
MIN 最小 6 mm²

