


S = $\begin{cases} \text{Ø10} - \text{Special IM 3001/*11} \\ \text{M8} - \text{Special IM 3601/*11} \end{cases}$

M2AA 080

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador

VC223: Flange ring FF 115 / Aro brida FF 115 // VC224: Flange ring FT 115 / Aro brida FT 115

Motor Dimension Print		Motor Type : M2AA 080	Document Nº : 3GZE 500 082-931.005
Description : Motor flange mounted special (2-pieces) IM3001/*11 or IM3601/*11 Motor con brida (2 piezas) IM3001/*11 o IM3601/*11			
Unit : Discret Automation & Motion - Fábrica Motores	Date : 2012-11-29	Issued by : ERM/ A. Caubera	Replaces :
		Approved by : ERM/ G. Blanes	Replaced by :
Asea Brown Boveri, S.A.	Customer Reference :		ABB