

1) Short

2) Large

S = { Ø15 – Special IM 2001/*11
 M12 – Special IM 2101/*11

M2AA 132

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador


VC253: Flange ring FF 265 / Aro brida FF 265 // VC254: Flange ring FT265 / Aro brida FT 265

Motor Dimension Print

Motor Type :
M2AA 132 Short

Document Nº :
3GZE 500 130-971.005

Description : Motor foot and flange mounted special (2-pieces) IM2001/*11 or IM2101/*11
 Motor con patas y brida (2 piezas) IM2001/*11 o IM2101/*11



Unit : Discret Automation & Motion - Fábrica Motores
 Date : 2012-12-13

Issued by : ERM/ A. Caubera
 Approved by : ERM/ G. Blanes

Replaces :
 Replaced by :

Asea Brown Boveri, S.A

Customer Reference :

ABB