



S = { Ø7 – Special IM 2001/*11
M6 – Special IM 2101/*11

M2AA 080

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador
VC216: Flange ring FF 85 / Aro brida FF 85 // VC218: Flange ring FT 85 / Aro brida FT 85

| | | | |
|--|---|-----------------------------|---------------------------------------|
| Motor Dimension Print | | Motor Type : M2AA 080 | Document Nº : 3GZE 500 080-911.005 |
| Description : Motor foot and flange mounted special (2-pieces) IM2001/*11 or IM2101/*11 Motor con patas y brida (2 piezas) IM2001/*11 o IM2101/*11 | | | |
| Unit : Discret Automation & Motion - Fábrica Motores Date : 2012-11-29 | Issued by : ERM/ A. Caubera Approved by : ERM/ G. Blanes | Replaces : Replaced by : | |
| Asea Brown Boveri, S.A. | Customer Reference : | ABB | |