



中国国家强制性产品认证证书

证书编号: 2024010302653171

认证委托人名称及地址

ABB 新会低压开关有限公司
广东省江门市新会区今古洲工业开发区

生产者名称及地址

ABB 新会低压开关有限公司
广东省江门市新会区今古洲工业开发区

生产企业名称及地址

ABB 新会低压开关有限公司
广东省江门市新会区今古洲工业开发区

产品名称和系列、型号、规格

隔离开关

OT63□□□, OT80□□□; Uimp:8kV;Ui:750V; OT63:Ith:63A; Ue/Ie:
AC-22A:AC415V,AC500V,AC690V/63A; AC-23A:AC415V/63A,AC500V/45A,AC690V/20A;
OT80:Ith:80A; Ue/Ie: AC-22A:AC415V,AC500V,AC690V/80A;
AC-23A:AC415V/75A,AC500V/58A,AC690V/20A; Icw:1500A/1s; Icm(峰值):2100A;
AC-22A,AC-23A; 3P,4P; 型号解释详见附页

产品标准和技术要求

GB/T 14048.3-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024)的要求,特发此证。

发证日期: 2024 年 07 月 05 日 有效期至: 2029 年 07 月 04 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验,
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





中国国家强制性产品认证证书

证书编号: 2024010302653171

证书附页: 第 1 页 共 1 页

型号的解释:

OT □ □ □ □
1 2 3 4 5

- 1、隔离开关: OT
- 2、AC-22A 的额定电流: 63、80
- 3、安装类型: F (底板和 DIN 导轨安装)、FT (柜门安装)
- 4、极数: 3、 4
- 5、第 4 极位置 (只有 4 极开关有此标识):
N1 (表示第 4 极在开关左边)、N2 (表示第 4 极在开关右边)

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010302653171

NAME AND ADDRESS OF THE APPLICANT

ABB Xinhui Low Voltage Switchgear Co.,Ltd.
Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province,
P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

ABB Xinhui Low Voltage Switchgear Co.,Ltd.
Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province,
P.R.China

NAME AND LOCATION OF THE FACTORY

ABB Xinhui Low Voltage Switchgear Co.,Ltd.
Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province,
P.R.China

PRODUCT NAME,MODEL AND SPECIFICATION

Switch-disconnectors

OT63□□□, OT80□□□; Uimp:8kV;Ui:750V; OT63:Ith:63A; Ue/Ie: AC-22A:AC415V,AC500V,AC690V/63A;
AC-23A:AC415V/63A,AC500V/45A,AC690V/20A; OT80:Ith:80A; Ue/Ie: AC-22A:AC415V,AC500V,AC690V/80A;
AC-23A:AC415V/75A,AC500V/58A,AC690V/20A; Icw:1500A/1s; Icm(Peak Value):2100A; AC-22A,AC-23A; 3P,4P

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.3-2017

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.05,2024

Valid until: Jul.04,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010302653171

Appendix: Page 1 of 1

OT ☐ ☐ ☐ ☐
1 2 3 4 5

- 1、隔离开关: OT
- 2、AC-22A 的额定电流: 63、80
- 3、安装类型: F (底板和 DIN 导轨安装)、FT (柜门安装)
- 4、极数: 3、4
- 5、第 4 极位置 (只有 4 极开关有此标识):
N1 (表示第 4 极在开关左边)、N2 (表示第 4 极在开关右边)



This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.