



EC DECLARATION OF CONFORMITY

(supplier's name) We ABB SACE S.p.A

(address) VIALE VICENZA, 61

36063 - MAROSTICA (VI)

declare under our sole responsibility that the product : _____

CABLE LADDERS H130

(name,type or model,lot,batch or serial number,possibly sources and numbers of items)

ARTICLES : IN ATTACHED

to which this declaration relates is in conformity with the following standard(s) or other
normative/documents EN 61537

(title and/or number and date of issue of the standard(s) or other normative document(s))

following the provisions of the Directive(s) 73/23 CEE MODIFIED BY 93/68 CEE

MAROSTICA, 11/03/2002

(Place and date of issue)

02

(last two digits of the year in which the mark was affixed)

ABB SACE S.p.A
TECHNICAL MANAGER
ENZO RIZZI


(seal, name and signature of authorized person)

Mod. 379 - 12/94 - 900

1SLT000018D00

Industrial metal trunkings

Cable ladders H 130



Article	For cable ladder base (mm)	Length (mm)	Unit/pack-metres
---------	----------------------------	-------------	------------------

Cable ladder

09 420	100	3000	3
09 421	200	3000	3
09 422	300	3000	3
09 423	400	3000	3
09 424	500	3000	3
09 425	600	3000	3

Snap-on cover

09 430	100	3000	3
09 431	200	3000	3
09 432	300	3000	3
09 433	400	3000	3
09 434	500	3000	3
09 435	600	3000	3


Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------

90° flat corner

Base		
09 460	100	1
09 461	200	1
09 462	300	1
09 463	400	1
09 464	500	1
09 465	600	1
Cover		
09 470	100	1
09 471	200	1
09 472	300	1
09 473	400	1
09 474	500	1
09 475	600	1

Industrial metal trunkings

Cable ladders H 130



Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------

45° flat corner

Base

09 500	100	1
09 501	200	1
09 502	300	1
09 503	400	1
09 504	500	1
09 505	600	1

Cover

09 510	100	1
09 511	200	1
09 512	300	1
09 513	400	1
09 514	500	1
09 515	600	1

Flat tee

Base

09 540	100	1
09 541	200	1
09 542	300	1
09 543	400	1
09 544	500	1
09 545	600	1

Cover

09 550	100	1
09 551	200	1
09 552	300	1
09 553	400	1
09 554	500	1
09 555	600	1

Flat cross


09 580	100	1
09 581	200	1
09 582	300	1
09 583	400	1
09 584	500	1
09 585	600	1

Cover

09 590	100	1
09 591	200	1
09 592	300	1
09 593	400	1
09 594	500	1
09 595	600	1

Industrial metal trunkings

Cable ladders H 130



Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------

Vertical inside and outside riser adjustable from 0° to 90°

09 620	100	1
09 621	200	1
09 622	300	1
09 623	400	1
09 624	500	1
09 625	600	1

Use straight covers for covering

90° vertical inside riser

09 974	100	1
09 975	200	1
09 976	300	1
09 977	400	1
09 978	500	1
09 979	600	1

Cover

09 934	100	1
09 935	200	1
09 936	300	1
09 937	400	1
09 938	500	1
09 939	600	1

90° vertical outside riser


09 992	100	1
09 993	200	1
09 994	300	1
09 995	400	1
09 996	500	1
09 997	600	1

Cover

09 955	100	1
09 956	200	1
09 957	300	1
09 958	400	1
09 959	500	1
09 960	600	1

Industrial metal trunkings

Cable ladders H 130



Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------

Concentric reducer

Base

09 660	200/100	1
09 661	300/100	1
09 662	300/200	1
09 663	400/200	1
09 664	400/300	1
09 665	500/300	1
09 666	500/400	1
09 667	600/400	1
09 668	600/500	1

Cover

09 670	200/100	1
09 671	300/100	1
09 672	300/200	1
09 673	400/200	1
09 674	400/300	1
09 675	500/300	1
09 676	500/400	1
09 677	600/400	1
09 678	600/500	1

Left reducer

Base


09 700	200/100	1
09 701	300/100	1
09 702	300/200	1
09 703	400/200	1
09 704	400/300	1
09 705	500/300	1
09 706	500/400	1
09 707	600/400	1
09 708	600/500	1

Cover

09 710	200/100	1
09 711	300/100	1
09 712	300/200	1
09 713	400/200	1
09 714	400/300	1
09 715	500/300	1
09 716	500/400	1
09 717	600/400	1
09 718	600/500	1

Industrial metal trunkings

Cable ladders H 130



Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------

Right reducer


Base		
09 740	200/100	1
09 741	300/100	1
09 742	300/200	1
09 743	400/200	1
09 744	400/300	1
09 745	500/300	1
09 746	500/400	1
09 747	600/400	1
09 748	600/500	1

Cover		
09 750	200/100	1
09 751	300/100	1
09 752	300/200	1
09 753	400/200	1
09 754	400/300	1
09 755	500/300	1
09 756	500/400	1
09 757	600/400	1
09 758	600/500	1

Overall dimensions pages 11/36 - 11/53

Industrial metal trunkings

Cable ladders H 130



Article	Description	Unit/pack-pieces
---------	-------------	------------------

Mechanical joint

Includes 2 plates complete with screws and nuts.

09 766	Straight joint	1/20
09 767	Horizontal adjustable joint	1/20
09 768	Vertical adjustable joint	1/10

Article	For reductions of (mm)	Unit/pack-pieces
---------	------------------------	------------------

Couplers for left and right reduction

09 806	50	1
09 807	100	1
09 808	200	1


Article	Length (mm)	Unit/pack-metres
---------	-------------	------------------

Metal divider

09 902	2000	2/10
--------	------	------

Industrial metal trunkings

Cable ladders H 130



Article	Description	Unit/pack-pieces
---------	-------------	------------------

Square and cover spacer

09 903	Spacer for cover H 50 mm	1/20
09 904	Square for fastening brackets – inner	1/50
09 905	Square for fastening brackets – outer	1/50

Fastening components

07 848	Round-headed M6x10 screw with nut	100
07 818	Hexagonal-headed M8x16 screw with nut	100
07 819	Hexagonal-headed M10x20 screw with nut	100

For fastening squares and spacers and for earth connections

Article	Length (mm)	Unit/pack-metres
---------	-------------	------------------

Earth cable

09 906	Cable with 4mm ² section	20
--------	-------------------------------------	----