

产品认证证书

II型自愿认证

证书编号: CQC2007010309251577

发证日期: 2021年11月23日

有效期至: 2031年11月23日

委托人名称 ABB France
及注册地址 11 Rue d' Arsonval 69680, Chassieu, FRANCE

制造商名称 ABB 新会低压开关有限公司
及注册地址 广东省江门市新会区今古洲工业开发区

生产企业名称 ABB 新会低压开关有限公司
及生产地址 广东省江门市新会区今古洲工业开发区

产品名称和系列、规格、型号 接触器
AS09,AS12,AS16,ASL09,ASL12,ASL16; 规格参数详见附件

产品标准和技术要求 GB/T 14048.4-2020

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月14日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

签发

刘江

谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0121353

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2007010309251577

Valid from: Nov.23,2021

Valid until:Nov.23,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
NAME AND LOCATION OF THE FACTORY	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
PRODUCT NAME, MODEL AND SPECIFICATION	Contactors AS09,AS12,AS16,ASL09,ASL12,ASL16; See the Appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.4-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

刘江

SIGNATURE

谢肇煦

CHINA QUALITY CERTIFICATION CENTRE



产品认证证书

II型自愿认证

证书编号: CQC2007010309251577

第 1 页 共 4 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 121353

上报参数:

AS09, AS12, AS16, ASL09, ASL12, ASL16

Ui: 690V;

Uimp:6kV;

AS09, ASL09:

Ith: 22A(螺钉接线),20A(弹簧接线);

AC-3:Ue/Ie:220/230/240/9A,400-415V/9A,440V/8A,500V/8A,690V/5A;

AC-4:Ue/Ie:230V/7.2A,400-415V/7.2A,500V/5.6A,690V/4A;

AC-1:Ue/Ie:690V/22A(螺钉接线),690V/20A(弹簧接线);

AC-8a:Ue/Ie:400V/12A;

AS12, ASL12:

Ith: 25A(螺钉接线),22A(弹簧接线);

AC-3:Ue/Ie:220/230/240/12A,400-415V/12A,440V/11A,500V/11A,690V/7A;

AC-4:Ue/Ie:230V/9.6A,400-415V/9A,500V/8A,690V/5.6A;

AC-1:Ue/Ie:690V/24A(螺钉接线),690V/22A(弹簧接线);

AC-8a:Ue/Ie:400V/16A;

AS16, ASL16:

Ith: 25A(螺钉接线),22A(弹簧接线);

AC-3:Ue/Ie:220/230/240/15.7A,400-415V/15.7A,440V/13.6A,500V/12.5A,690V/9A;

AC-4:Ue/Ie:230V/12.6A,400-415V/12.4A,500V/10A,690V/7.2A;

AC-1:Ue/Ie:690V/24A(螺钉接线),690V/22A(弹簧接线);

AC-8a:Ue/Ie:400V/22A;

Us:AC:24V,42V,48V,110V,115V,220V,230V,240V,400V,415V(50/60Hz),

120V,277V(60Hz),380V(50Hz),

DC:12V,24V,48V,60V,110V,125V,220V,240V;

IP20;

极数: 3P;

配用的辅助触头:(AS,ASL)

Ith:10A;

AC-15:Ue/Ie: 24-127V/6A, 220-240V/4A, 380-440V/3A, 500-690V/2A;

DC-13:Ue/Ie: 24V/6A, 48V/2.8A, 72V/1A, 110V/0.55A, 125V/0.55A, 220-250V/0.3A;



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2007010309251577

第 2 页 共 4 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 121353

AS-30-10,ASL30-10:1NO,
AS-30-01,ASL30-01:1NC,
AS-30-32,ASL30-32:3NO2NC

型号解释:

ASL 16-3 0-10 S-81

线圈代号: 见表 2.1

接线方式: 有 S 为弹簧接线,
无 S 为线夹螺钉接线

10: 常开辅助触点对数 1;

01: 常闭辅助触点对数 1; |

32: 常开辅助触点对数 3,
常闭辅助触点对数 2

常闭主触点对数 0

常开主触点对数 3

400V, AC3 应用类别下可参考的额定工作电流

09:9A; 12:12A; 16:15.7A

系列名称: AS 系列接触器

AS 表示控制回路为交流

ASL 表示控制回路为直流



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2007010309251577

第 3 页 共 4 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 121353

表 2.1:

额定工作电压		线圈代号
50Hz	60Hz	
24V	24V	20
42V	42V	21
48V	48V	22
110V	110V	23
115V	115V	24
	120V	16
220V	220V	25
230V	230V	26
240V	240V	27
-	277V	17
380V	-	13
400V	400V	28
415V	415V	29
-		
12V DC	-	80
24V DC	-	81
48V DC	-	83
60V DC	-	84
110V DC	-	86
125V DC	-	87
220V DC	-	88



中国质量认证中心



产品认证证书

II型自愿认证


证书编号: CQC2007010309251577

第 4 页 共 4 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 121353

240V	DC	-	89
------	----	---	----



中国质量认证中心

