


Earth bonds & clamps

Earth bars



Earth bar with twin disconnecting link

Part no.	Description	Length (mm)	Weight each (kg)
Copper earth bar			
LK207-6	6 way	550	2.80
LK207-8	8 way	650	3.20
LK207-10	10 way	800	3.80
LK207-12	12 way	900	4.20
LK207-14	14 way	1000	4.60
LK207-16	16 way	1100	5.00
LK207-18	18 way	1200	5.40
LK207-20	20 way	1350	6.00
LK207-22	22 way	1450	6.40
LK207-24	24 way	1550	6.80
LK207-26	26 way	1650	7.20
LK207-28	28 way	1800	7.90
LK207-30	30 way	1900	8.30
Tinned copper earth bar			
LK207-6-T	6 way	550	2.80
LK207-8-T	8 way	650	3.20
LK207-10-T	10 way	800	3.80
LK207-12-T	12 way	900	4.20
LK207-14-T	14 way	1000	4.60
LK207-16-T	16 way	1100	5.00
LK207-18-T	18 way	1200	5.40
LK207-20-T	20 way	1350	6.00
LK207-22-T	22 way	1450	6.40
LK207-24-T	24 way	1550	6.80
LK207-26-T	26 way	1650	7.20
LK207-28-T	28 way	1800	7.90
LK207-30-T	30 way	1900	8.30

Standards

BS 7430

- Fix using countersunk wood screws 1½" No. 12 (Part no. SW110) and wall plugs (Part no. PS310)
- Standard width x height: 90 mm x 77 mm