


**M2AA 090**  
(\* ) Except 090\_LD

S =  $\begin{cases} \text{Ø13} - \text{Special IM 3001/*11} \\ \text{M10} - \text{Special IM 3601/*11} \end{cases}$

**Additional information:**

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador

VC233: Flange ring FF 165 / Aro brida FF 165 // VC234: Flange ring FT 165 / Aro brida FT 165

<b>Motor Dimension Print</b>	Motor Type : <b>M2AA 090 (*)</b>	Document Nº : <b>3GZE 500 092-951.005</b>
Description : <b>Motor flange mounted special (2-pieces) IM3001/*11 or IM3601/*11</b> <b>Motor con brida (2 piezas) IM3001/*11 o IM3601/*11</b>		
Unit : <b>Discret Automation &amp; Motion - Fábrica Motores</b> Date : <b>2012-12-03</b>	Issued by : <b>ERM/ A. Caubera</b> Approved by : <b>ERM/ G. Blanes</b>	Replaces : Replaced by :
<b>Asea Brown Boveri, S.A.</b>	Customer Reference :	<b>ABB</b>