

Item	Qty	Description of products and services	Price per unit	Amount
------	-----	--------------------------------------	----------------	--------

		<p>Zone Module, 4-fold, LF</p> <p>The MG/E Zone Module is used to expand the zones of the GM/A 8.1 KNX Security Panel. The module is mounted in the panel housing of the KNX Security Panel. Up to two MG/E Zone Modules can be used for each panel. The modules each have 4 zones for connection of security detectors. In addition, configurable status information can be displayed via 3 switchable outputs. The zone module meets the VdS guidelines for class A, B, and C, as well as DIN EN 50 131 Grades 1-3 and ISO/IEC 62 642 Grades 1-3.</p> <p>Applications:</p> <ul style="list-style-type: none"> - Connection via the Security Bus (S-Bus 1) - Freely configurable entry functions for connection of security detectors (door/window contacts, magnetic contacts, glass break detector, locking detector, technical detector, hold up detector, tamper detector) - Freely selectable detector monitoring (N/C and N/O contacts with/without 2.7 kOhm EOL resistor, setting line with tamper detection, N/C contacts with alarm and tamper detection) - Freely configurable transistor outputs for status information <p>Protection type: IP 30 to DIN EN 60 529</p> <p>Modular installation device for installation in panel housing Dimensions (H x W x D): 90 x 63 x 25 mm</p> <p>Manufacturer: ABB STOTZ-KONTAKT</p> <p>Type: MG/E 4.4.1</p> <p>Material:..... Labor:.....</p>	Carry:	
--	--	---	--------	--

		MGE_441_AT_EN_V2-0 2CDC 513 069 D0201	Carry:	
--	--	--	--------	--

MG/E 4.4.1

MG/E 4.4.1