


FurseWELD

Offset type lug



Offset type lug - FurseWELD

Part No.	Stranded Conductor					
	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)
L0101	20	3	40	10	8.5	40
L0102-FU	25	3	45	12	8.5	40
L0103-FU	25	3	45	12	10.5	40
L0104	31	6	50	15	10.5	40
L0105	31	6	50	16	12.5	40
L0106	38	5	55	18	10.5	40
L0107	38	6	55	18	10.5	40
L0108	38	6	55	20	12.5	40
L0109	50	6	75	25	10.5	60
L0110	50	6	75	25	12.5	60

