

Federal Pacific roll-in replacement breaker availability

Medium voltage

Original Breaker Type	KV	MVA	New kA	AMPS	AMVAC	ADVAC
DST2-15-500, 1200A	15	500	25	1200	*	
DST2-15-500, 2000A	15	500	25	2000	*	
DST2-15-750, 1200A	15	750	40	1200	*	
DST2-15-750, 2000A	15	750	40	2000	*	
DST2-5-150, 1200A	5	150	31.5	1200	*	
DST2-5-150, 2000A	5	150	31.5	2000	*	
DST2-5-250, 1200A	5	250	31.5	1200	*	
DST2-5-250, 2000A	5	250	31.5	2000	*	
DST2-7.5-250, 1200A	7	250	31.5	1200	*	
DST2-7.5-250, 2000A	7	250	31.5	2000	*	
DST2-7.5-500, 1200A	7	500	40	1200	*	
DST2-7.5-500, 2000A	7	500	40	2000	*	
DST-5-150, 1200A	5	150	31.5	1200	*	
DST-5-250, 1200A	5	250	31.5	1200	*	

* Available, ** Contact factory, (Blank) Not available

Low voltage

Original Type	Frame	Direct replacement		Cradle in cradle	
		MO	EO	MO	EO
DMB-25	600	*	*		
FP-25	600	*	*		
FP-75	3000	*	*	*	*
FPS-4-50	1600			*	*
FPS-4-50H	2000			*	*
FPS-50	1600	*	*		
FPS-5-75	3000			*	*

* Available, ** Contact factory, (Blank) Not available