



EC DECLARATION OF CONFORMITY

(supplier's name) We ABB SACE S.p.A

(address) VIALE VICENZA, 61

36063 - MAROSTICA (VI)

declare under our sole responsibility that the product : _____

CABLE LADDERS H60

(name, type or model, lot, batch or serial number, possibly sources and numbers of items)

ARTICLES : IN ATTACHED

to which this declaration relates is in conformity with the following standard(s) or other
normative/documents EN 61357

(title and/or number and date of issue of the standard(s) or other normative document(s))

following the provisions of the Directive(s) 73/23 CEE MODIFIED BY 93/68 CEE

MAROSTICA, 11/03/2002

(Place and date of issue)

02

(last two digits of the year in which the mark was affixed)

ABB SACE S.p.A
TECHNICAL MANAGER
ENZO RIZZI


(seal, name and signature of authorized person)

Mod. 379 - 12/94 - 900

1SLT000016D00

Industrial metal trunkings

Cable ladders H 60



| Article | Cable ladder base (mm) | Length (mm) | Unit/pack-metres |
|---------|------------------------|-------------|------------------|
|---------|------------------------|-------------|------------------|

Cable ladder

| | | | |
|--------|-----|------|---|
| 09 400 | 100 | 3000 | 3 |
| 09 401 | 200 | 3000 | 3 |
| 09 402 | 300 | 3000 | 3 |
| 09 403 | 400 | 3000 | 3 |
| 09 404 | 500 | 3000 | 3 |
| 09 405 | 600 | 3000 | 3 |

Snap-on cover

| | | | |
|--------|-----|------|---|
| 09 430 | 100 | 3000 | 3 |
| 09 431 | 200 | 3000 | 3 |
| 09 432 | 300 | 3000 | 3 |
| 09 433 | 400 | 3000 | 3 |
| 09 434 | 500 | 3000 | 3 |
| 09 435 | 600 | 3000 | 3 |


| Article | For cable ladder base (mm) | Unit/pack-pieces |
|---------|----------------------------|------------------|
|---------|----------------------------|------------------|

90° flat corner

| | | |
|--------|-----|---|
| Base | | |
| 09 440 | 100 | 1 |
| 09 441 | 200 | 1 |
| 09 442 | 300 | 1 |
| 09 443 | 400 | 1 |
| 09 444 | 500 | 1 |
| 09 445 | 600 | 1 |
| Cover | | |
| 09 470 | 100 | 1 |
| 09 471 | 200 | 1 |
| 09 472 | 300 | 1 |
| 09 473 | 400 | 1 |
| 09 474 | 500 | 1 |
| 09 475 | 600 | 1 |

Industrial metal trunkings

Cable ladders H 60



| Article | For cable ladder base (mm) | Unit/pack-pieces |
|---------|----------------------------|------------------|
|---------|----------------------------|------------------|

45° flat corner

| | | |
|--------|-----|---|
| 09 480 | 100 | 1 |
| 09 481 | 200 | 1 |
| 09 482 | 300 | 1 |
| 09 483 | 400 | 1 |
| 09 484 | 500 | 1 |
| 09 485 | 600 | 1 |

Cover

| | | |
|--------|-----|---|
| 09 510 | 100 | 1 |
| 09 511 | 200 | 1 |
| 09 512 | 300 | 1 |
| 09 513 | 400 | 1 |
| 09 514 | 500 | 1 |
| 09 515 | 600 | 1 |

Flat tee

Base

| | | |
|--------|-----|---|
| 09 520 | 100 | 1 |
| 09 521 | 200 | 1 |
| 09 522 | 300 | 1 |
| 09 523 | 400 | 1 |
| 09 524 | 500 | 1 |
| 09 525 | 600 | 1 |

Cover

| | | |
|--------|-----|---|
| 09 550 | 100 | 1 |
| 09 551 | 200 | 1 |
| 09 552 | 300 | 1 |
| 09 553 | 400 | 1 |
| 09 554 | 500 | 1 |
| 09 555 | 600 | 1 |

Flat cross

Base

| | | |
|--------|-----|---|
| 09 560 | 100 | 1 |
| 09 561 | 200 | 1 |
| 09 562 | 300 | 1 |
| 09 563 | 400 | 1 |
| 09 564 | 500 | 1 |
| 09 565 | 600 | 1 |

Cover

| | | |
|--------|-----|---|
| 09 590 | 100 | 1 |
| 09 591 | 200 | 1 |
| 09 592 | 300 | 1 |
| 09 593 | 400 | 1 |
| 09 594 | 500 | 1 |
| 09 595 | 600 | 1 |

Industrial metal trunkings

Cable ladders H 60



| Article | For cable ladder base (mm) | Unit/pack-pieces |
|---------|----------------------------|------------------|
|---------|----------------------------|------------------|

Vertical inside and outside riser adjustable from 0° to 90°

| | | |
|--------|-----|---|
| 09 600 | 100 | 1 |
| 09 601 | 200 | 1 |
| 09 602 | 300 | 1 |
| 09 603 | 400 | 1 |
| 09 604 | 500 | 1 |
| 09 605 | 600 | 1 |

Use straight covers for covering

90° vertical inside riser

| Base | | |
|--------|-----|---|
| 09 962 | 100 | 1 |
| 09 963 | 200 | 1 |
| 09 964 | 300 | 1 |
| 09 965 | 400 | 1 |
| 09 966 | 500 | 1 |
| 09 967 | 600 | 1 |

| Cover | | |
|--------|-----|---|
| 09 920 | 100 | 1 |
| 09 921 | 200 | 1 |
| 09 922 | 300 | 1 |
| 09 923 | 400 | 1 |
| 09 924 | 500 | 1 |
| 09 925 | 600 | 1 |


90° vertical outside riser

| | | |
|--------|-----|---|
| 09 980 | 100 | 1 |
| 09 981 | 200 | 1 |
| 09 982 | 300 | 1 |
| 09 983 | 400 | 1 |
| 09 984 | 500 | 1 |
| 09 985 | 600 | 1 |

| Cover | | |
|--------|-----|---|
| 09 941 | 100 | 1 |
| 09 942 | 200 | 1 |
| 09 943 | 300 | 1 |
| 09 944 | 400 | 1 |
| 09 945 | 500 | 1 |
| 09 946 | 600 | 1 |

Industrial metal trunkings

Cable ladders H 60



| Article | For cable ladder base (mm) | Unit/pack-pieces |
|---------|----------------------------|------------------|
|---------|----------------------------|------------------|

Concentric reducer


| Base | | |
|--------|---------|---|
| 09 640 | 200/100 | 1 |
| 09 641 | 300/100 | 1 |
| 09 642 | 300/200 | 1 |
| 09 643 | 400/200 | 1 |
| 09 644 | 400/300 | 1 |
| 09 645 | 500/300 | 1 |
| 09 646 | 500/400 | 1 |
| 09 647 | 600/400 | 1 |
| 09 648 | 600/500 | 1 |
| Cover | | |
| 09 670 | 200/100 | 1 |
| 09 671 | 300/100 | 1 |
| 09 672 | 300/200 | 1 |
| 09 673 | 400/200 | 1 |
| 09 674 | 400/300 | 1 |
| 09 675 | 500/300 | 1 |
| 09 676 | 500/400 | 1 |
| 09 677 | 600/400 | 1 |
| 09 678 | 600/500 | 1 |

Left reducer

| 09 680 | 200/100 | 1 |
|--------|---------|---|
| 09 681 | 300/100 | 1 |
| 09 682 | 300/200 | 1 |
| 09 683 | 400/200 | 1 |
| 09 684 | 400/300 | 1 |
| 09 685 | 500/300 | 1 |
| 09 686 | 500/400 | 1 |
| 09 687 | 600/400 | 1 |
| 09 688 | 600/500 | 1 |
| Cover | | |
| 09 710 | 200/100 | 1 |
| 09 711 | 300/100 | 1 |
| 09 712 | 300/200 | 1 |
| 09 713 | 400/200 | 1 |
| 09 714 | 400/300 | 1 |
| 09 715 | 500/300 | 1 |
| 09 716 | 500/400 | 1 |
| 09 717 | 600/400 | 1 |
| 09 718 | 600/500 | 1 |

Industrial metal trunkings

Cable ladders H 60



| Article | For cable ladder base (mm) | Unit/pack-pieces |
|---------|----------------------------|------------------|
|---------|----------------------------|------------------|

Right reducer

Base


| | | |
|--------|---------|---|
| 09 720 | 200/100 | 1 |
| 09 721 | 300/100 | 1 |
| 09 722 | 300/200 | 1 |
| 09 723 | 400/200 | 1 |
| 09 724 | 400/300 | 1 |
| 09 725 | 500/300 | 1 |
| 09 726 | 500/400 | 1 |
| 09 727 | 600/400 | 1 |
| 09 728 | 600/500 | 1 |

Cover

| | | |
|--------|---------|---|
| 09 750 | 200/100 | 1 |
| 09 751 | 300/100 | 1 |
| 09 752 | 300/200 | 1 |
| 09 753 | 400/200 | 1 |
| 09 754 | 400/300 | 1 |
| 09 755 | 500/300 | 1 |
| 09 756 | 500/400 | 1 |
| 09 757 | 600/400 | 1 |
| 09 758 | 600/500 | 1 |

Industrial metal trunkings

Cable ladders H 60



| Article | Description | Unit/pack-pieces |
|---------|-------------|------------------|
|---------|-------------|------------------|

Mechanical joint

Includes 2 plates complete with screws and nuts.

| | | |
|--------|-----------------------------|------|
| 09 760 | Straight joint | 1/20 |
| 09 761 | Horizontal adjustable joint | 1/20 |
| 09 762 | Vertical adjustable joint | 1/10 |

| Article | For reductions of (mm) | Unit/pack-pieces |
|---------|------------------------|------------------|
|---------|------------------------|------------------|

Couplers for left and right reduction

| | | |
|--------|-----|---|
| 09 800 | 50 | 1 |
| 09 801 | 100 | 1 |
| 09 802 | 200 | 1 |


| Article | Length (mm) | Unit/pack-metres |
|---------|-------------|------------------|
|---------|-------------|------------------|

Metal divider

| | | |
|--------|------|------|
| 09 900 | 2000 | 2/10 |
|--------|------|------|

Industrial metal trunkings

Cable ladders H 60



| Article | Description | Unit/pack-pieces |
|---------|-------------|------------------|
|---------|-------------|------------------|

Square and cover spacer

| | | |
|--------|---------------------------------------|------|
| 09 903 | Spacer for cover H 50 mm | 1/20 |
| 09 904 | Square for fastening brackets – inner | 1/50 |
| 09 905 | Square for fastening brackets – outer | 1/50 |

Fastening components

| | | |
|--------|--|-----|
| 07 848 | Round-headed M6x10 screw with nut | 100 |
| 07 818 | Hexagonal-headed M8x16 screw with nut | 100 |
| 07 819 | Hexagonal-headed M10x20 screw with nut | 100 |

For fastening squares and spacers and for earth connections.

| Article | Length (mm) | Unit/pack-metres |
|---------|-------------|------------------|
|---------|-------------|------------------|

Earth cable

| | | |
|--------|-------------------------------------|----|
| 09 906 | Cable with 4mm ² section | 20 |
|--------|-------------------------------------|----|