



EC DECLARATION OF CONFORMITY

(supplier's name) We ABB SACE S.p.A

(address) VIALE VICENZA, 61

36063 - MAROSTICA (VI)

declare under our sole responsibility that the product : _____

FEEDER AND CABLE TRUNKINGS - 04 SERIES

(name,type or model,lot,batch or serial number,possibly sources and numbers of items)

ARTICLES : IN ATTACHED

to which this declaration relates is in conformity with the following standard(s) or other
normative/documents CEI 23-32

RELEASE FROM IMQ INSTITUTE BY D.A.T. N° E7158

(title and/or number and date of issue of the standard(s) or other normative document(s))

following the provisions of the Directive(s) 73/23 CEE MODIFIED BY 93/68 CEE

MAROSTICA, 11/03/2002

(Place and date of issue)

02

(last two digits of the year in which the mark was affixed)

ABB SACE S.p.A
TECHNICAL MANAGER
ENZO RIZZI

(seal, name and signature of authorized person)

Mod. 379 - 12/94 - 900

1SLT000003D00

Feeder and cable trunkings

Design styled cable trunkings



Article	Dimensions WxH (mm)	Colour	Unit/pack-pieces
---------	---------------------	--------	------------------

Cable trunkings IP40

44 010*	50x68 [IMQ]	White	28
44 012	100x68 [IMQ]	White	14
44 014	150x68 [IMQ]	White	10
44 016	200x68 [IMQ]	White	8

* Cable trunking feeders for electric circuits

Article	Trunking base (mm)	Colour	Unit/pack-pieces
---------	--------------------	--------	------------------

90° flat corner, IP40

44 050	50 [IMQ]	White	10/30
44 052	100 [IMQ]	White	8/16
44 054	150 [IMQ]	White	1/10

For 200-mm flat branch connections use art. 44 092

Junction box IP40

For cable trunkings and branch connections with skirting and H 10, 17, 30 mini-trunkings. Complete with separator.

44 090	50/100 [IMQ]	White	1/10
44 092	150/200 [IMQ]	White	1/4

Internal corner IP40

44 130	50 [IMQ]	White	10/20
44 132	100 [IMQ]	White	1/20
44 134	150 [IMQ]	White	1/10
44 136	200 [IMQ]	White	1/10

External corner IP40

44 170	50 [IMQ]	White	10/20
44 172	100 [IMQ]	White	1/20
44 174	150 [IMQ]	White	1/10
44 176	200 [IMQ]	White	1/8


End cap IP40

44 210	50 [IMQ]	White	20
44 212	100 [IMQ]	White	20
44 214	150 [IMQ]	White	20
44 216	200 [IMQ]	White	15

Feeder and cable trunkings

Design styled cable trunkings

3



Article	Length (mm)	Colour	Unit/pack-pieces
---------	-------------	--------	------------------

Divider

Snaps onto the base of all design styled cable trunking feeders.

44 040	200 [IMQ]	White	52
--------	-----------	-------	----

Article	Trunking base (mm)	Colour	Unit/pack-pieces
---------	--------------------	--------	------------------

Switch-socket base interaxis 83.5 mm

To install 3 modular devices.

44 352	100 [IMQ]	White	1/20
44 354	150 [IMQ]	White	1/10
44 356	200 [IMQ]	White	1/10

Box for telephone socket

To install a unified telephone socket.

44 434	150 [IMQ]	White	1/10
44 436	200 [IMQ]	White	1/10

Box interaxis 60/67 mm

To install 2 modular or fastener devices.

44 452	100 [IMQ]	White	1/20
44 454	150 [IMQ]	White	1/10
44 456	200 [IMQ]	White	1/10

Universal adjustable box

For IEC 16 and 32 A plugs.

44 514	150 [IMQ]	White	1/10
44 516	200 [IMQ]	White	1/10

Blank box 73x73 mm

44 554	150 [IMQ]	White	1/10
44 556	200 [IMQ]	White	1/10

Technical details

- Boxes snap onto the base of the trunkings
 - Boxes come complete with plate and two flat joints for the cover
 - Cable clamps for safely anchoring cables
- Minimum installation height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with CEI 64-8 Standard

Feeder and cable trunkings

Accessories for design styled cable trunkings



Article	Trunking base (mm)	Colour	Unit/pack-pieces
---------	--------------------	--------	------------------

Cover joint

44 250	50 [IMQ]	White	20
44 252	100 [IMQ]	White	20
44 254	150 [IMQ]	White	20
44 256	200 [IMQ]	White	20

Flat joint for trunkings

44 291	Universal [IMQ]	White	20
--------	-----------------	-------	----

Cable retainer

04 322	100 [IMQ]	Black	20
04 324	150 [IMQ]	Black	20
04 326	200 [IMQ]	Black	20

MCBs kit

To fasten any kind of 17.5x45 mm modular device.

Four modules

44 634	150 [IMQ]	White	10/40
44 636	200 [IMQ]	White	5/20

Ten modules

44 654	150 [IMQ]	White	10/40
44 656	200 [IMQ]	White	5/20

MCBs enclosure 17.5x45 mm

Four modules

44 680	50/100 [IMQ]	White	1/10
--------	--------------	-------	------

Ten modules

44 682	150/200 [IMQ]	White	1/4
--------	---------------	-------	-----