



**M2AA 090**  
(\* Except 090\_LD)

S =  $\begin{cases} \text{Ø11} - \text{Special IM 2001/*11} \\ \text{M8} - \text{Special IM 2101/*11} \end{cases}$

**Additional information:**

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador

VC226: Flange ring FF 130 / Aro brida FF 130 // VC227: Flange ring FT 130 / Aro brida FT 130

<b>Motor Dimension Print</b>	Motor Type : <b>M2AA 090 (*)</b>	Document Nº : <b>3GZE 500 090-941.005</b>
Description : <b>Motor foot and flange mounted special (2-pieces) IM2001/*11 or IM2101/*11</b> <b>Motor con patas y brida (2 piezas) IM2001/*11 o IM2101/*11</b>		
Unit : <b>Discret Automation &amp; Motion - Fábrica Motores</b> Date : <b>2012-12-03</b>	Issued by : <b>ERM/ A. Caubera</b> Approved by : <b>ERM/ G. Blanes</b>	Replaces : Replaced by :
<b>Asea Brown Boveri, S.A.</b>	Customer Reference :	<b>ABB</b>