







**Blocco a chiave e lucchetti in posizione inserito - estratto prova - estratto**  
**Key lock and padlock in connected - isolated for test - withdrawn position**  
**Schlüssel- und Schloßverriegelung in Stellung eingeschoben - ausgefahren Prüfstellung - ausgefahren**  
**Verrouillage par clé et cadenas en position embroché - débroché essai - débroché**  
**Bloqueo a llave y por candados en posición insertado - extraído prueba - extraído**







**E**




**F**



**G**




**H**




**I**

Per blocco a lucchetti utilizzare 1-3 lucchetti Ø 4  
 Use 1-3 padlocks with a 4 mm hasp diameter for the padlock device  
 Für die Schloßverriegelung 1 bis 3 Vorhängeschlösser mit Bügel  $\varnothing$  4 mm verwenden  
 Pour verrouillage par cadenas, utiliser 1-3 cadenas 4 mm  
 Para bloqueo por candados utilizar 1-3 candados de 4 mm


**Istruzione per blocco a chiave e lucchetti in posizione di sezionato prova e sezionato.**  
**Instruction for key lock and padlock device in test isolated and racked-out position**  
**Anweisung für Schlüssel- und Schloßverriegelung in Prüf- und Trennstellung.**  
**Instruction pour verrouillage par clé et cadenas en position de sectionné en essai et sectionné**  
**Instrucciones para el bloqueo a llave y por candados en posición de seccionado prueba y seccionado**



**L**



**M**



**N**