



S = { Ø7 – Special IM 2001/*11
M6 – Special IM 2101/*11

M2AA 080

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador

VC219: Flange ring FT 100 / Aro brida FT 100 // VC220: Flange ring FF 100 / Aro brida FF 100

Motor Dimension Print		Motor Type : M2AA 080	Document N° : 3GZE 500 080-921.005
Description : Motor foot and flange mounted special (2-pieces) IM2001/*11 or IM2101/*11 Motor con patas y brida (2 piezas) IM2001/*11 o IM2101/*11			
Unit : Discret Automation & Motion - Fábrica Motores Date : 2012-11-29	Issued by : ERM/ A. Caubera Approved by : ERM/ G. Blanes	Replaces : Replaced by :	
Asea Brown Boveri, S.A.	Customer Reference :		ABB